



Item #	Code	Description	Spaces	Height	Shipping Weight	1-9	10-24	25-99	100-249
RoHS 19" (48.3cm) Steel Lockboxes - 9" (22.9cm) Depth Allows Rack Mountable Security									
Safely secure gear in the LBX series of lockboxes. 3 and 4 rack space models are available, both are 9" (22.9cm) deep. Black powder coat finish.									
LBX-3	A	19" (48.3cm) Rack Mountable Lockbox	3	5.25 in (13.3cm)	11 lbs (5.0kg)	101.34	99.31	95.26	76.00
LBX-4	A	19" (48.3cm) Rack Mountable Lockbox	4	7.00 in (17.8cm)	12 lbs (5.5kg)	110.13	107.93	103.52	82.60
RoHS 19" (48.3cm) Steel Utility Drawer in 2, 3 and 4 Rack Space Heights									
These steel utility drawers are available in two, three and four rack space heights for storing equipment and supplies. Full extension ball bearing slides smoothly extending to a full 14" (35.6cm). Inside dimensions 15.88" x 14.5" (40.3cm x 36.8cm). Knockouts in rear allow cable pass through. Black powder coat finish.									
UD-2	B	19" (48.3cm) Rack Mountable Utility Drawer	2	3.50 in (8.9cm)	16 lbs (7.3kg)	133.27	130.60	125.27	99.95
UD-3	B	19" (48.3cm) Rack Mountable Utility Drawer	3	5.25 in (13.3cm)	19 lbs (8.6kg)	141.89	139.05	133.38	106.42
UD-4	B	19" (48.3cm) Rack Mountable Utility Drawer	4	7.00 in (17.8cm)	21 lbs (9.5kg)	163.47	160.20	153.66	122.60
RoHS 3.5" (8.9cm) and 5.25" (13.3cm) High (2 and 3 Rack Spaces) Heavy Duty Shelves for 19" (48.3cm) Racks									
Two heavy duty shelves are available for 19" (48.3cm) rack panels. Cantilever shelf is 17" (43.2cm) deep and occupies three rack spaces vertically. The center weight shelf is 18" (45.7cm) deep in total and occupies two rack spaces vertically. Both shelves have vented bottoms. Color: Matte black.									
U317	C	19" (48.3cm) Rack Mountable Heavy Duty Cantilever Shelf, 17" (43.2cm) Dp	3	5.25 in (13.3cm)	10 lbs (4.5kg)	78.22	76.66	73.53	58.66
U2MS	D	19" (48.3cm) Rack Mountable Heavy Duty Center Weight Shelf, 18" (45.7cm) Dp	2	3.50 in (8.9cm)	9 lbs (4.1kg)	83.27	81.60	78.27	62.45
RoHS 19" (48.3cm) Rackmount Slide-Away Computer Keyboard System									
The rackmount computer keyboard system occupies only 1.75" (4.4cm) (1 space) and features a high quality keyboard with built in trackball. A built in cable support arm provides secure cable management.									
RM-KB-LCD17	E	19" (48.3cm) Rackmount Slide-Away 17" (43.2cm) LCD Monitor, Keyboard and Touchpad	1	1.75 in (4.4cm)	35 lbs (15.9kg)	2459.39	2410.20	2311.83	1844.54
RM-KB	F	19" (48.3cm) Rackmount Computer Keyboard with Trackball	1	1.75 in (4.4cm)	16 lbs (7.3kg)	527.14	516.60	495.51	395.36
RoHS 19" (48.3cm) Rackmount Sliding Shelves									
The rackmount shelves slide out giving easy access to equipment. A telescopic rear support offers flexibility in rack mounting depths. Each shelf requires a minimum rack depth of 14.75" (37.5cm).									
SSL	G	19" (48.3cm) Sliding Shelf w/14" x 16.75" (35.6cm x 42.5cm) Work Surface, 35 lb Capacity	1	1.75 in (4.4cm)	9 lbs (4.1kg)	103.63	101.56	97.41	77.72
SS	H	19" (48.3cm) Sliding Shelf w/14.75" x 17.5" (37.5cm x 44.5cm) Work Surface, 50 lb Capacity	1+	2.40 in (6.1cm)	15 lbs (6.8 kg)	153.42	150.35	144.21	115.06
RoHS High Capacity Stationary Shelf, 4 Point Mount									
VSA-1626	I	Adjustable Heavy Duty Vented Rackshelf	<1	1.50 in (3.8cm)	12 lbs (5.5kg)	118.68	116.31	111.56	89.01
VSA-2744	I	Adjustable Heavy Duty Vented Rackshelf	<1	1.50 in (3.8cm)	19 lbs (8.6kg)	146.20	143.28	137.43	109.65
RoHS 19" (48.3cm) Rack Filler Panels									
A variety of 19" (48.3cm) rack filler panels allow installers to give a custom look to their rack installation while allowing proper thermal venting.									
PR175BLK	J	1.75" (4.4cm) Blank Filler Panel, Solid Steel	1	1.75 in (4.4cm)	1 lb (0.5kg)	20.85	19.18	17.51	15.85
PR35BLK	J	3.50" (8.9cm) Blank Filler Panel, Solid Steel	2	3.50 in (8.9cm)	2 lbs (0.9kg)	27.45	25.25	23.06	20.86
PR175-EVTBLK	K	1.75" (4.4cm) Blank Filler Panel, Vertical Vented Steel	1	1.75 in (4.4cm)	1 lb (0.5kg)	11.69	11.46	10.99	8.77
PR35-EVTBLK	K	3.50" (8.9cm) Blank Filler Panel, Vertical Vented Steel	2	3.50 in (8.9cm)	1 lb (0.5kg)	15.29	14.98	14.37	11.47
PR175-VTPBLK	L	1.75" (4.4cm) Blank Filler Panel, Horizontal Vented Steel	1	1.75 in (4.4cm)	1 lb (0.5kg)	27.38	26.83	25.74	20.54
PR35-VTPBLK	L	3.50" (8.9cm) Blank Filler Panel, Horizontal Vented Steel	2	3.50 in (8.9cm)	1 lb (0.5kg)	29.90	29.30	28.11	22.42
FILTER	M	5.25" x 19" (13.3cm x 48.3cm) Rack Filter	3	5.25 in (13.3cm)	1 lb (0.5kg)	38.86	38.08	36.53	29.14
QTFP-2	M	5.25" x 19" (13.3cm x 48.3cm) Panel with Dual 4.5" (11.4cm) Fans	3	5.25 in (13.3cm)	5 lbs (2.3kg)	140.79	137.97	132.34	105.59

"L-com's e-mails pointing out answers to questions and getting people to start using your website as a knowledge based resource is an excellent marketing idea, but also an excellent resource. Educating our colleagues is a vital part of keeping our technological superiority over the competition whether it is business or national defense." - Joe Gannatal, Supervisory Electronics Engineer, U.S. Navy