



Item #	Code	Description	1-9	10-24	25-99	100-249	250-499
--------	------	-------------	-----	-------	-------	---------	---------

Universal Series Sub-Panels Featuring Coaxial and Mini DIN Couplers

This Universal sub-panel series offers connections for data transmission over coaxial and DIN style connectors. Installers can choose the sub-panel that fits their specific connection needs. Panel choices offer feed-thru style couplers in either 2 or 4 connections per panel. Blank panels are also available for further customization. All panels come equipped with four pre-tapped holes to accept the four 6-32 mounting screws which are supplied.

USP-A1	A	Blank Sub-Panel with 1 0.5" (1.3cm) D-Hole, Black Aluminum	4.95	4.75	4.55	4.36	4.16
USP-A2	B	Blank Sub-Panel with 2 0.5" (1.3cm) D-Holes, Black Aluminum	4.95	4.75	4.55	4.36	4.16
USP-A4	C	Blank Sub-Panel with 4 0.5" (1.3cm) D-Holes, Black Aluminum	4.95	4.75	4.55	4.36	4.16
USP221B	A	Blank Sub-Panel with 1 0.5" (1.3cm) D-Hole, Black Steel	4.95	4.75	4.55	4.36	4.16
USP222B	B	Blank Sub-Panel with 2 0.5" (1.3cm) D-Holes, Black Steel	4.95	4.75	4.55	4.36	4.16
USP224B	C	Blank Sub-Panel with 4 0.5" (1.3cm) D-Holes, Black Steel	4.95	4.75	4.55	4.36	4.16
USP2BB	D	Sub-Panel with 2 BNC Couplers	13.95	13.39	12.83	12.28	11.72
USP4BB	D	Sub-Panel with 4 BNC Couplers	21.95	21.07	20.19	19.32	18.44
USP2BDB	E	Sub-Panel with 2 BNC Couplers, Insulated	14.95	14.35	13.75	13.16	12.56
USP4BDB	E	Sub-Panel with 4 BNC Couplers, Insulated	24.95	23.95	22.95	21.96	20.96
USP1NB	F	Sub-Panel with 1 Type N Coupler	19.95	19.15	18.35	17.56	16.76
USP2MD6B	G	Sub-Panel with 2 Mini DIN 6 Couplers	22.98	22.06	21.14	20.22	19.30
USP4MD6B	G	Sub-Panel with 4 Mini DIN 6 Couplers	39.98	38.38	36.78	35.18	33.58
USP2RCAB	H	Sub-Panel with 2 RCA Couplers, Red/White	12.98	12.46	11.94	11.42	10.90
USP3RCAB	H	Sub-Panel with 3 RCA Couplers, Yellow/Red/White	15.98	15.34	14.70	14.06	13.42
USP3RCA-CB	H	Sub-Panel with 3 RCA Couplers, Green/Blue/Red	15.98	15.34	14.70	14.06	13.42
USP1SVID2RCAB	H	Sub-Panel with 1 Mini DIN 4 and 2 RCA Couplers	20.98	20.14	19.30	18.46	17.62
USP2TB	I	Sub-Panel with 2 TNC Couplers	14.98	14.38	13.78	13.18	12.58
USP2TDB	J	Sub-Panel with 2 TNC Couplers, Insulated	16.98	16.30	15.62	14.94	14.26
USP2FB	K	Sub-Panel with 2 Type F Couplers	8.98	8.62	8.26	7.90	7.54
USP2FDB	L	Sub-Panel with 2 Type F Couplers, Insulated	10.98	10.54	10.10	9.66	9.22