

SWTC-32005T
(Front View)



SWTC-32005T
(Rear View)



GEP66424T



GEP63109T



GEP22000S-L



SWTC-FS605NA



SWTC-FS105NA



SWTC-GS105NA



SWTC-GS724T

Item #	Description	List Price
--------	-------------	------------

Unicom's Unmanaged 10/100 Mbps Ethernet Switches - 5 or 8 RJ45 Ports

The Mini-Switch 5 and 8 are super compact 10/100Base-TX switches. These parts represent the newest generation in Ethernet switching technology by supporting both 10 and 100 Mbps speeds, half or full-duplex transmission modes and auto MDI/MDIX crossover checking. Units include a 9 VDC power supply.

SWTC-32005T	Unicom 5 Port 10/100 Mbps Unmanaged Ethernet Switch	25.00
-------------	---	-------

Unicom DynaGST 24 Port Gigabit Switch with SFP Slots

The DynaGST 2402G Gigabit Ethernet switches are an ideal solution for solving traffic congestion at the core of the network. They offer auto-negotiating 10/100/1000Base-T Gigabit Ethernet ports that can significantly improve your network backbone performance. The DynaGST switches provide two mini GBIC Gigabit slots for Gigabit speed network connections. The DynaGST Gigabit Ethernet switches feature an Auto MDI/MDIX function for each port and support store-and-forward switching.

GEP22000S-L	GBIC SFP Transceiver, 1000SX, LC, Multimode, 500m	99.00
GEP22100L-L	GBIC SFP Transceiver, 1000LX, LC, Single mode, 10km	199.00
GEP66424T	24 Port 10/100/1000Base-T with Four Slots for SFP	479.00

Unicom 8 Port 10/100 Managed Switch with 1000Base-T Port and SFP Slot

Unicom's SmartGST-900M managed switch is the newest generation of fast Ethernet switching technology. Eight 10/100Base-TX auto sensing, auto MDI/MDIX ports provide a completely flexible high-performance non-blocking full wire speed solution. Enhanced by its many features including one SFP GBIC port, one 1000Base-T port, VLAN tagging, port trunking, spanning tree, and broadcast storm filters, this switch is an ideal solution for campus and enterprise networks. The SmartGST-900M management features also include port-based, dynamic and static VLANs, GVRP, IGMP Snooping, port mirroring and port security. The SFP GBIC and 1000Base-T port offer high-speed long haul connections that eliminate bottlenecks to create the ideal backbone.

GEP63109T	8 Port 10/100 Managed Switch with 1000Base-T Port and SFP Slot	329.00
GEP22000S-L	GBIC SFP Transceiver, 1000SX, LC, Multimode, 500m	99.00
GEP22100L-L	GBIC SFP Transceiver, 1000LX, LC, Single mode, 10km	199.00

Netgear 5 and 8 Port 10/100 Ethernet Switches (Plastic Case)

Netgear's 5-port Fast Ethernet Switch offers a simple solution for instantly expanding your network. This auto-switching Ethernet connection makes it easy to link up to 5 PC or Ethernet devices to your network. It supports both Windows and Macintosh platforms at speeds of 10 or 100 Mbps over Ethernet cables and works with virtually every operating system.

SWTC-FS605NA	Netgear 5 Port 10/100Mbps Fast Ethernet Switch	29.00
SWTC-FS608NA	Netgear 8 Port 10/100Mbps Fast Ethernet Switch	49.00

Netgear 5, 8 and 16 Port 10/100 Ethernet Switches

Netgear's 10/100Mbps Fast Ethernet Switches provide your LAN with economical, high-speed, 10/100 Mbps auto-sensing connectivity. Just plug in your Ethernet cables and connect a power cord and you network is up and running. These switches are engineered without the need for an internal fan, thus providing silent operation. The switches feature a very compact footprint and a sturdy metal case for years of dependable use.

SWTC-FS105NA	Netgear 10/100MB 5 Port RJ45 Switch	32.00
SWTC-FS108NA	Netgear 10/100MB 8 Port RJ45 Switch	52.00
SWTC-FS108P	Netgear 10/100MB 8 Port w/ 4 POE Ports Switch	159.00
SWTC-FS116NA	Netgear 10/100MB 16 Port RJ45 Switch	85.00

Netgear 5 and 8 Port 10/100/1000 Ethernet Switches

Netgear's Gigabit Switches offer users high-speed network connections in a compact cost effective switch. The GS series switches feature auto-negotiation between 10, 100, and 1000MB connections allowing users to migrate to higher speeds over time. With Auto uplink and full duplex operation, these Netgear Gigabit switches make connections simple and fast. Includes an external power supply.

SWTC-GS105NA	Netgear 10/100/1000MB 5-Port RJ45 Switch	79.00
SWTC-GS108NA	Netgear 10/100/1000MB 8-Port RJ45 Switch	119.00

Netgear 10/100/1000 24-Port plus 2 SFP Gigabit Ethernet Switch

This Netgear 24-port Gigabit Ethernet switch is high on value and capability. With 24 10/100/1000 Mbps ports, each capable of powering 2,000 Mbps of data throughput in full-duplex mode, plus two optional fiber ports, the SWTC-GS724T provides a fast backbone and connects servers or power users, delivering large amounts of multimedia, image, and video information in no time at all. In addition, an intuitive, web-browser interface offers simple Smart Switch management, making it a snap to monitor switch performance, configure ports, even set up port trunks, VLANs, and traffic prioritization. Alternatively, use SNMP-based software to manage your Smart Switch.

SWTC-GS724T	Netgear 10/100/1000MB 24-Port plus 2 SFP Gigabit Ethernet Switch	349.00
-------------	--	--------

