

Item #	Description	List Price
--------	-------------	------------

Planet Indoor/Outdoor IR Analog Surveillance Camera 30 Meters

The Planet CAM-PTIR338 can be used indoors or outdoors and is the perfect solution for today's surveillance requirements. This camera features zero-lux illumination and 36 IR illuminators which are built around the lens to provide clear vision at night. Via new LED technology, the built-in illuminators ensure high-quality monochrome images in total darkness as far as 30 meters. In addition, the CAM-PTIR338 features a waterproof enclosure constructed of rugged aluminum. The CAM-PTIR338 IR camera provides reliable operation in any environment.

CAM-PTIR338	Planet Indoor/Outdoor IR Analog Camera 30 Meters	139.00
-------------	--	--------

Planet Indoor/Outdoor IR Analog Surveillance Camera 15 Meters

The Planet CAM-PTIR138 features zero-lux illumination and 12 IR illuminators which are built around the lens to provide clear vision at night. Via new LED technology, the built-in illuminators ensure high-quality monochrome images in total darkness as far as 15 meters. In addition, the CAM-PTIR138 features a waterproof enclosure constructed of rugged aluminum. The CAM-PTIR138 IR camera provides reliable operation in any environment.

CAM-PTIR138	Planet Indoor/Outdoor IR Analog Camera 15 Meters	99.00
-------------	--	-------

Planet Indoor/Outdoor IR Vandal Proof Analog Surveillance Camera 15 Meters

The Planet CAM-PTIVP52 provides a rugged, vandal proof video surveillance solution. The CAM-PTIVP52's unique design prevents annoying halo issues that are sometimes seen with IR dome cameras. This design blocks the refracted IR rays from entering into the lens and provides a clear picture. Additionally, the CAM-PTIVP52 features zero-lux illumination and 6 IR illuminators which are built around the lens to provide clear vision up to 15 meters at night.

CAM-PTIVP52	Planet Indoor/Outdoor IR Vandal Proof Analog Camera 15 Meters	199.00
-------------	---	--------

Planet ICA-PT107 Wired and Wireless IP Surveillance Cameras

Planet's powerful and economical ICA-107 Series Internet cameras feature integrated microcomputers and high quality CMOS digital image sensors, enabling them to display high quality live streaming video over a LAN or the Internet. The advanced motion detection feature supported by the ICA-107 Series can notify users via email or ftp of any detected movement.

ICA-PT107	Planet IP Surveillance Camera	100.00
ICA-PT107W	Planet Wireless IP Surveillance Camera 802.11b/g	125.00

Planet ICA-PT601/PT651 Indoor/Outdoor Speed Dome IP Surveillance Cameras

Planet's ICA-PT601/PT651, indoor/outdoor speed dome Internet cameras, offer pan, tilt and zoom to control over TCP/IP networks. The ICA-PT601/PT651 features a 220X zooming (22x optical zoom, 10x digital zoom), auto focus, auto iris as well as fast, accurate and continuous 360 panning operations. With 32 presets, 4 camera tour configurations and combined with motion detection, these unparalleled surveillance functions satisfy all of your demanding surveillance and remote monitoring requirements. The ICA-PT601 is designed for indoor use and the ICA-PT651 features a rugged IP66 rated housing and can be used outdoors. Additional features include simultaneous 10 user access, support for both MPEG-4 and M-JPEG and two-way audio support.

ICA-PT601NT	Planet Indoor Speed Dome IP Surveillance Camera	1489.00
ICA-PT651NT	Planet Outdoor Speed Dome IP Surveillance Camera	1899.00

Planet IVS-H120 H.264 Internet Video Server

The Planet H.264 Internet Video Server, IVS-H120, allows the conversion of any analog camera into a fully functional IP camera. It integrates the next generation video compression technology – H.264 and can compress the video file size for a user to transfer the images on the Internet easily. It can stream digital video over an office network in the same way as current IP cameras do. By connecting the IVS-H120 with an analog camera, all elements of an existing surveillance system can be upgraded to a new IP surveillance system. The IVS-H120 can send live video and audio through the internet allowing user's access via a web browser anywhere in the world.


The IVS-H120 supports surveillance with 2-Way audio. With a speaker connected to the IVS-H120, the administrator can talk to anyone remotely at the camera site. The IVS-H120 also supports the Planet Media Converter Chassis (PTMC1500). A maximum of 15 IVS-H120's can be installed in the media converter chassis at one time. Power to the IVS-H120 is supplied by the media converter chassis and can be centrally managed.

The IVS-H120 supports Multi-Profile to transfer different video streams in H.264, MPEG-4 and M-JPEG to different users simultaneously. Moreover, the resolutions can differ from one user to another. This state-of-the-art design is extremely versatile and fits in a multitude of network environments. Up to 20 users can access to the IVS-H120 at the same time.

IVS-H120	Planet Internet Video Server	169.00
----------	------------------------------	--------



Turn traditional surveillance to IP network surveillance



"L-com is by far the best company that I've done business with in a very long time. The product quality, shipping response, and customer service are second to none. Thanks for the great service!" - Travis T.