

Item #	Description	List Price
Brady Portable Label Printers		
The BMP™21 Portable Label Printer is an all-in-one labeler for voice/datacom, electrical and general industrial crews. With label materials designed specifically for harsh environments, the BMP™21 portable printer can quickly and easily create clear, legible labels that stay stuck for years - despite extreme temperatures and curved or highly textured surfaces. With more than 400 different label options, the new BMP71 Label Printer is Brady's most versatile portable printer. This easy to use labeler can help you cut material waste, save time, and create labels more efficiently than ever before. Make labels faster than ever before with built-in design wizards, high speed print, 1.5" (3.8cm) per second, and storage space for over 100,000 label files.		
BMP21	Brady Portable Label Printer	139.00
BMP71	Brady Portable Label Printer	895.00

Brady IDXPRT Handheld Labeling System

The IDXPRT is the first handheld cartridge based labeling system that can print die-cut labels, self-laminating labels and sleeves as well as continuous tapes. You name it IDXPRT prints it. Choose from two keyboard layouts, then select from a wide range of label materials engineered just for your application. That includes wire and cable markers, panel, rack and frame ID, facilities labels and specialty labels for labs and workspaces. The IDXPRT can be used with self-lams, sleeves and 90+ label styles including continuous tapes. Additionally, the IDXPRT can print on materials up to 1.5" (3.8cm) wide and prints characters up to 1.25" (3.2cm). It also provides 82 symbols plus bar codes.

IDXPRT-ABC	Brady IDXPRT Handheld Labeling System (ABC Layout)	399.95
IDXPRT-KEY	Brady IDXPRT Handheld Labeling System (Keyboard Layout)	399.95

Brady TLS2200™ Premium Thermal Transfer Label Printer

The TLS2200 system offers the lightweight of a hand-held printer (2.75lbs), while providing the superior capabilities of thermal transfer printing. The Brady printer features a two-line liquid crystal display and produces smear proof, ultra clear print quality and faster output than most other printers on the market. Useful for printing barcodes as well as text and numbers with crystal clear accuracy on labels up to 2" (5.1cm) wide. This means you can now print labels for wire markers, patch panels, circuit boards, cable markers and more, faster and easier than ever before. Includes a 6-month manufacturer's warranty.

TLS2200	Premium Brady Thermal Transfer Printer	849.00
R6210	Replacement Ribbon for TLS2200	23.95
TLS2200-BP	Replacement Battery	95.00

Item #	Description	Qty / Uom	List Price
--------	-------------	-----------	------------

Brady BMP21 Cable Labels

M21-375-499	Nylon Cloth White, 0.375"W x 16"H (1cm W x 4.9m H)	1/Roll	22.00
M21-500-499	Nylon Cloth White, 0.50"W x 16"H (1.3cm W x 4.9m H)	1/Roll	22.95
M21-750-499	Nylon Cloth White, 0.75"W x 16"H (1.9cm W x 4.9m H)	1/Roll	23.99

Note: Many other label types are available; contact your L-com Sales Representative for more information

Brady BMP71 Cable Labels

M71-17-351	Tamper-resistant Vinyl White, 1.00"W x 0.50"H (2.5cm W x 1.3cm H)	500/Roll	51.95
M71-30-427-AW	Self Laminating Vinyl, 1.50"W x 0.750"H (3.8cm W x 1.9cm H)	250/Roll	35.49
M71-31-351	Tamper-resistant Vinyl White, 1.50"W x 1.00"H (3.8cm W x 2.5cm H)	250/Roll	39.95
M71-20-351	Tamper-resistant Vinyl White, 2.00"W x 1.00"H (5.1cm W x 2.5cm H)	100/Roll	31.95

Note: Many other label types are available; contact your L-com Sales Representative for more information

Brady IDXPRT Cable Labels

These labels are ideal for marking data cabling. The B-427 vinyl self-laminating material offers superior abrasion resistance and resists dirt, oils, solvents and water. Each label features a clear, non-printed area, which wraps around and over laminates the printed text. The IDXPRT automatically "multiple repeats" your text in the white print area. These labels are UL Recognized and support a temperature range of -94°F to 158°F (-70°C to 70°C).

XSL-102-427	Self Laminating Vinyl White, 0.50"W x 1.25"H (1.3cm W x 3.2cm H)	250/Roll	27.95
XSL-103-427	Self Laminating Vinyl White, 1.00"W x 1.25"H (2.5cm W x 3.2cm H)	250/Roll	44.95
XSL-115-427	Self Laminating Vinyl White, 1.50"W x 1.25"H (3.8cm W x 3.2cm H)	250/Roll	39.95
XSL-29-427	Self Laminating Vinyl White, 0.50"W x 1.50"H (1.3cm W x 3.8cm H)	500/Roll	49.95
XSL-30-427	Self Laminating Vinyl White, 0.75"W x 1.50"H (1.9cm W x 3.8cm H)	250/Roll	37.95

Note: Many other label types available, call your L-com Sales Representative for more information.

Brady TLS2200 Cable Labels

PTL19427	Cable Labels, 1.0"L x 1.0"W x .375"H (2.5cm L x 2.5cm W x 1cm H)	250/Roll	29.95
PTL31427	Cable Labels, 1.0"L x 1.5"W x .50"H (2.5cm L x 3.8cm W x 1.3cm H)	250/Roll	39.95
PTL21427	Cable Labels, 1.0"L x 2.5"W x .75"H (2.5cm L x 6.4cm W x 1.9cm H)	100/Roll	24.95

Note: Many other label types available, call your L-com Sales Representative for more information.

Item #	Description	Qty / Uom	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----------	-----	-------	-------	---------	---------

RoHS Cable Labels - Wraparound Style, 3 Sizes to Choose From

CL0515	Cable Labels, .50"L x 1.5"W x .50"H (1.3cm L x 3.8cm W x 1.3cm H)	30/Roll	5.95	5.83	5.71	5.59	5.47
CL1150	Cable Labels, 1.0"L x 1.5"W x .50"H (2.5cm L x 3.8cm W x 1.3cm H)	30/Roll	7.95	7.79	7.63	7.47	7.31
CL1375	Cable Labels, 1.0"L x 3.75"W x 1.0"H (2.5cm L x 9.5cm W x 2.5cm H)	30/Roll	5.95	5.83	5.71	5.59	5.47

Note: CL Series labels are not intended for use with Brady printers.



To see our entire product offering go to...L-com.com