



Item #	Description	1-9	10-24	25-99	100-249	250-499
RG59B/U 75 Ohm Impedance	• Center Conductor: 22 AWG solid bare copper covered steel	NOMINAL ATTENUATION				
	• Shielding: Bare copper braid (95% coverage)					
	• Insulation: Polyethylene	MHz	db/100 ft	db/100m		
	• Jacket: Black PVC	50	2.4	7.9		
	• Operating Temperature: -40°C - +80°C	100	3.4	11.1		
	200	4.9	16.1			
	400	7.0	23.0			
	1000	12.0	39.3			

RG59B/U - 75 Ohm Coaxial Cables with Inline BNC Plug to BNC Jack

CC59B-MF-1	RG59B Cable, BNC Male / Female Bulkhead, 1.0 ft	12.00	11.28	10.56	9.84	9.12
CC59B-MF-3	RG59B Cable, BNC Male / Female Bulkhead, 3.0 ft	13.00	12.22	11.44	10.66	9.88
CC59B-MF-6	RG59B Cable, BNC Male / Female Bulkhead, 6.0 ft	14.50	13.63	12.76	11.89	11.02
CC59B-MF-10	RG59B Cable, BNC Male / Female Bulkhead, 10.0 ft	16.50	15.51	14.52	13.53	12.54
CC59B-MF-15	RG59B Cable, BNC Male / Female Bulkhead, 15.0 ft	19.00	17.86	16.72	15.58	14.44
CC59B-MF-25	RG59B Cable, BNC Male / Female Bulkhead, 25.0 ft	24.00	22.56	21.12	19.68	18.24
CC59B-MF-50	RG59B Cable, BNC Male / Female Bulkhead, 50.0 ft	36.50	34.31	32.12	29.93	27.74

RG59B/U - 75 Ohm Coaxial Cables with One Inline BNC to One Right Angle BNC Plug

CC59B-1HR	RG59B Cable, BNC Male / 90° Male, 1.0 ft	11.25	10.80	10.35	9.90	9.45
CC59B-1.5HR	RG59B Cable, BNC Male / 90° Male, 1.5 ft	11.50	11.04	10.58	10.12	9.66
CC59B-2HR	RG59B Cable, BNC Male / 90° Male, 2.0 ft	11.75	11.28	10.81	10.34	9.87
CC59B-2.5HR	RG59B Cable, BNC Male / 90° Male, 2.5 ft	12.00	11.52	11.04	10.56	10.08
CC59B-3HR	RG59B Cable, BNC Male / 90° Male, 3.0 ft	12.25	11.76	11.27	10.78	10.29
CC59B-4HR	RG59B Cable, BNC Male / 90° Male, 4.0 ft	12.75	12.24	11.73	11.22	10.71
CC59B-5HR	RG59B Cable, BNC Male / 90° Male, 5.0 ft	13.25	12.72	12.19	11.66	11.13
CC59B-7.5HR	RG59B Cable, BNC Male / 90° Male, 7.5 ft	14.50	13.92	13.34	12.76	12.18
CC59B-10HR	RG59B Cable, BNC Male / 90° Male, 10.0 ft	15.75	15.12	14.49	13.86	13.23

RG59B/U - 75 Ohm Coaxial Cables with Two Right Angle BNC Plugs

CC59B-1HR2	RG59B Cable, BNC 90° Male / 90° Male, 1.0 ft	15.00	14.40	13.80	13.20	12.60
CC59B-1.5HR2	RG59B Cable, BNC 90° Male / 90° Male, 1.5 ft	15.25	14.64	14.03	13.42	12.81
CC59B-2HR2	RG59B Cable, BNC 90° Male / 90° Male, 2.0 ft	15.50	14.88	14.26	13.64	13.02
CC59B-2.5HR2	RG59B Cable, BNC 90° Male / 90° Male, 2.5 ft	15.75	15.12	14.49	13.86	13.23
CC59B-3HR2	RG59B Cable, BNC 90° Male / 90° Male, 3.0 ft	16.00	15.36	14.72	14.08	13.44
CC59B-4HR2	RG59B Cable, BNC 90° Male / 90° Male, 4.0 ft	16.50	15.84	15.18	14.52	13.86
CC59B-5HR2	RG59B Cable, BNC 90° Male / 90° Male, 5.0 ft	17.00	16.32	15.64	14.96	14.28
CC59B-7.5HR2	RG59B Cable, BNC 90° Male / 90° Male, 7.5 ft	18.25	17.52	16.79	16.06	15.33
CC59B-10HR2	RG59B Cable, BNC 90° Male / 90° Male, 10.0 ft	19.50	18.72	17.94	17.16	16.38

RG59B/U - 75 Ohm Coaxial Cables with Two Inline Molded Type F Plugs

CCF59B-1	RG59B Cable, Type F Male / Male, 1.0 ft	4.50	4.32	4.14	3.96	3.78
CCF59B-3	RG59B Cable, Type F Male / Male, 3.0 ft	5.50	5.28	5.06	4.84	4.62
CCF59B-6	RG59B Cable, Type F Male / Male, 6.0 ft	7.00	6.72	6.44	6.16	5.88
CCF59B-9	RG59B Cable, Type F Male / Male, 9.0 ft	8.50	8.16	7.82	7.48	7.14
CCF59B-12	RG59B Cable, Type F Male / Male, 12.0 ft	10.00	9.60	9.20	8.80	8.40
CCF59B-25	RG59B Cable, Type F Male / Male, 25.0 ft	16.50	15.84	15.18	14.52	13.86
CCF59B-50	RG59B Cable, Type F Male / Male, 50.0 ft	29.00	27.84	26.68	25.52	24.36
CCF59B-100	RG59B Cable, Type F Male / Male, 100.0 ft	54.00	51.84	49.68	47.52	45.36

RG6/U - 75 Ohm Coaxial Cables with Two Inline Type F Plugs

This series features low loss RG6 coaxial cable popular in transmission of television signal over cable. Features include: gold flash on connector surfaces, molded strain relief on the connector for superior protection and a captivated gold plated center conductor, not the cable's center conductor typically found in lower quality assemblies.

RG6/U 75 Ohm Impedance	NOMINAL ATTENUATION				
	MHz	db/100 ft	db/100m		
	50	1.5	4.9		
	100	2.1	6.9		
	200	3.1	10.2		
400	4.5	14.8			
1000	7.3	23.9			

CCF6-1	RG6 Cable, Type F Male / Male, 1.0 ft	5.75	5.18	4.60	4.02	3.45
CCF6-3	RG6 Cable, Type F Male / Male, 3.0 ft	6.75	6.08	5.40	4.72	4.05
CCF6-6	RG6 Cable, Type F Male / Male, 6.0 ft	8.25	7.43	6.60	5.78	4.95
CCF6-9	RG6 Cable, Type F Male / Male, 9.0 ft	9.75	8.78	7.80	6.82	5.85
CCF6-12	RG6 Cable, Type F Male / Male, 12.0 ft	11.25	10.13	9.00	7.87	6.75
CCF6-25	RG6 Cable, Type F Male / Male, 25.0 ft	17.75	15.98	14.20	12.43	10.65
CCF6-50	RG6 Cable, Type F Male / Male, 50.0 ft	30.25	27.23	24.20	21.17	18.15
CCF6-100	RG6 Cable, Type F Male / Male, 100.0 ft	55.25	49.73	44.20	38.67	33.15

RG6/U - 75 Ohm Coaxial Cable with One Inline Type F Plug and One Type F Bulkhead Jack

CCF6-MF-1	RG6 Cable, Type F Male / Female Bulkhead, 1.0 ft	6.40	6.02	5.63	5.25	4.86
CCF6-MF-6	RG6 Cable, Type F Male / Female Bulkhead, 6.0 ft	10.15	9.54	8.93	8.32	7.71
CCF6-MF-12	RG6 Cable, Type F Male / Female Bulkhead, 12.0 ft	14.65	13.77	12.89	12.01	11.13
CCF6-MF-25	RG6 Cable, Type F Male / Female Bulkhead, 25.0 ft	24.40	22.94	21.47	20.01	18.54
CCF6-MF-50	RG6 Cable, Type F Male / Female Bulkhead, 50.0 ft	43.15	40.56	37.97	35.38	32.79

2008 Master Catalog 1.0

Shop at **L-com.com** or call **1-800-343-1455**
E-mail: sales@L-com.com Fax: 978-689-9484

We want to help you!
See a complete list of free tips, tutorials and videos at L-com.com/Resources

