

Item #	Code	Description	1-9	10-24	25-99	100-249	250-499
--------	------	-------------	-----	-------	-------	---------	---------

3.5 GHz, 4.9 GHz, 5.1 GHz, 5.3 GHz, 5.4 GHz and 5.8 GHz Patch Antennas

L-com's extensive line of patch antennas that cover frequencies from 3.5 to 5.8 GHz are ideal for applications such as WiMAX and public safety. Several of the patch antennas are broadband/multi-band antennas that eliminate the need to purchase different antennas for each frequency being used. This simplifies installations since the same antenna can be used for a wide array of wireless applications.

✓RoHS 3.5 GHz Patch Antennas

HG3509P-NF	A	8dBi, 4in Square, 12in Pigtail with NF Connector	39.99	35.99	31.99	27.99	23.99
HG3514P-NF	A	14dBi, 8in Square, 12in Pigtail with NF Connector	49.99	44.99	39.99	34.99	29.99

✓RoHS 4.9 GHz Patch Antennas

HG4953P	A	8dBi, 4in Square, Broadband, Integral SM Connector	49.99	44.99	39.99	34.99	29.99
HG4911P	A	11dBi, 4in Square, Integral SM Connector	49.99	44.99	39.99	34.99	29.99

✓RoHS 5.3 GHz Patch Antennas

HG5308P	A	8dBi, 4in Square, Integral SM Connector	39.99	35.99	31.99	27.99	23.99
HG5311P	A	11dBi, 4in Square, Integral SM Connector	49.99	44.99	39.99	34.99	29.99

✓RoHS 5.4 GHz Patch Antennas

HG5408P	A	8dBi, 4in Square, Integral SM Connector	39.99	38.39	36.79	33.99	29.99
HG5411P	A	11dBi, 4in Square, Integral SM Connector	49.99	47.99	45.99	42.49	37.49
HG5419P	A	19dBi, 7in Square, Integral FM Connector	49.99	47.49	44.99	42.49	CALL

✓RoHS 5.8 GHz Patch Antennas

HG5808P	A	8dBi, 4in Square, Integral SM Connector	39.99	35.99	31.99	27.99	23.99
HG5811P	A	11dBi, 4in Square, Integral SM Connector	49.99	44.99	39.99	34.99	29.99
HG5819P	A	19dBi, 7in Square, Integral FM Connector	49.99	47.49	44.99	42.49	CALL
HG5158P	A	8dBi, 4in Square, Broadband, Integral SF Connector	49.99	44.99	39.99	34.99	29.99
HG5158-23P	A	23dBi, 12in Square, Broadband, Integral NF Connector	79.99	77.59	75.19	72.79	70.39

2.4 GHz Mobile Mount Antennas - Built for Demanding Mobile Applications

Our extensive line of magnetic mount and mast mount mobile Omnidirectional antennas are perfect for demanding mobile applications including law enforcement, construction vehicles, and mobile metering. Several styles are offered with many frequency and gain choices supporting IEEE 802.11b/g/n.

- All weather construction
- IEEE 802.11b/g/n
- Bluetooth® and Wi-Fi
- Magnetic and mast mount options
- RoHS compliant

✓RoHS Magnetic Mobile Mounts

HMA6-RSP05	A	RP-SMA Jack to RP-SMA Plug, 5ft 100-Series	14.99	13.49	11.99	10.49	CALL
HMA6-RSP10	A	RP-SMA Jack to RP-SMA Plug, 10ft 100-Series	19.99	17.99	15.99	13.99	CALL
HMA6-RTP05	A	RP-SMA Jack to RP-TNC Plug, 5ft 100-Series	14.99	13.49	11.99	10.49	CALL
HMA6-RTP10	A	RP-SMA Jack to RP-TNC Plug, 10ft 100-Series	19.99	17.99	15.99	13.99	CALL
HMA1-NFA10	B	NMO to N-Female, 10ft 195-Series	19.95	17.95	15.96	13.96	CALL
HMA1-NMA10	B	NMO to N-Male, 10ft 195-Series	19.95	17.95	15.96	13.96	CALL
HMA1-RSPA10	B	NMO to RP-SMA Plug, 10ft 195-Series	19.95	17.95	15.96	13.96	CALL
HMA1-RTPA10	B	NMO to RP-TNC Plug, 10ft 195-Series	19.95	17.95	15.96	13.96	CALL
HMA3-NFA10	C	N-Female to N-Female, 10ft 195-Series	24.99	22.49	19.99	17.49	14.99
HMA3-NMA10	C	N-Female to N-Male, 10ft 195-Series	24.99	22.49	19.99	17.49	14.99
HMA3-RSPA10	C	N-Female to RP-SMA Plug, 10ft 195-Series	24.99	22.49	19.99	17.49	14.99
HMA3-RTPA10	C	N-Female to RP-TNC Plug, 10ft 195-Series	24.99	22.49	19.99	17.49	14.99

✓RoHS 2.4 GHz Antennas with Magnetic Mobile Mounts

HG2403MGU-NM	E	3dBi, Dual Band, 10ft Cable with NM Connector	34.99	31.49	27.99	24.49	20.99
HG2403MGU-RSP	E	3dBi, Dual Band, 10ft Cable with RP-SMA Connector	39.99	35.99	31.99	27.99	23.99
HG2403MGU-RTP	E	3dBi, Dual Band, 10ft Cable with RP-TNC Connector	39.99	35.99	31.99	27.99	23.99
HG2403MGURW-NM	F	3dBi, White Radome, 10ft Cable with NM Connector	34.99	31.49	27.99	24.49	20.99
HG2403MGURW-RSP	F	3dBi, White Radome, 10ft Cable with RP-SMA Connector	39.99	35.99	31.99	27.99	23.99
HG2403MGURW-RTP	F	3dBi, White Radome, 10ft Cable with RP-TNC Connector	39.99	35.99	31.99	27.99	23.99
HG2403MGURB-NM	F	3dBi, Black Radome, 10ft Cable with NM Connector	34.99	31.49	27.99	24.49	20.99
HG2403MGURB-RSP	F	3dBi, Black Radome, 10ft Cable with RP-SMA Connector	39.99	35.99	31.99	27.99	23.99
HG2403MGURB-RTP	F	3dBi, Black Radome, 10ft Cable with RP-TNC Connector	39.99	35.99	31.99	27.99	23.99
HG2405MGU-NM	D	5dBi, 10ft Cable with NM Connector	39.99	38.39	36.79	33.99	29.99
HG2405MGU-RSP	D	5dBi, 10ft Cable with RP-SMA Connector	49.99	47.99	45.99	42.49	37.49
HG2405MGU-RTP	D	5dBi, 10ft Cable with RP-TNC Connector	49.99	47.99	45.99	42.49	37.49
HG2409MGU-NF	H	8.5dBi, 10ft Cable with NF Connector	64.99	61.09	57.19	53.29	49.39
HG2409MGU-NM	H	8.5dBi, 10ft Cable with NM Connector	64.99	61.09	57.19	53.29	49.39
HG2409MGU-RSP	H	8.5dBi, 10ft Cable with RP-SMA Connector	74.99	70.49	65.99	61.49	56.99

✓RoHS 2.4 GHz Mobile Mount Antennas

HG2403U-NMO	E	3dBi, Dual Band, Integral NMO Connector	29.99	26.99	23.99	20.99	17.99
HG2403UR-NMOW	F	3dBi, White Radome, Integral NMO Connector	29.99	26.99	23.99	20.99	17.99
HG2403UR-NMOB	F	3dBi, Black Radome, Integral NMO Connector	29.99	26.99	23.99	20.99	17.99
HG2405U-NMO	D	5dBi, Integral NMO Connector	19.99	17.99	15.99	13.99	11.99
HG2405UR-NMO	G	5dBi, Black Radome, Flex-Base, Integral NMO Connector	99.99	89.99	79.99	69.99	59.99
HG2409U	H	8.5dBi, Integral NM Connector	49.99	45.99	41.99	37.99	33.99



[HG3514P-NF](#) Shown with HGX-PMT08 window mount kit. See [page 13](#) for more mounting options.



Mounting: Magnetic mounting system is available for permanent installations.



Informative e-mail newsletters

Our newsletters are packed with tips, tutorials, product info and downloads! L-com.com/NewsletterSignUp