



Item #	Code	Description	1-9	10-24	25-99	100-249	250-499
--------	------	-------------	-----	-------	-------	---------	---------

**900 MHz, 1.9 GHz, 2.4/5.8 GHz and 3.5 GHz Rubber Duck Antennas**

These high performance Omnidirectional rubber duck antennas provide broad coverage and multiple gain options. HyperLink Brand flexible rubber duck antennas feature tilt-and-swivel connectors allowing them to be used vertically, at a right angle, or any angle in-between. Suitable as a replacement RF antenna for radios, wireless video transmitters and receivers, as well as digital spread spectrum radios.

**Extensive List of Antennas for Many, Many Applications**

- Tilt-and-swivel connectors
- Point-to-point systems
- Point-to-multipoint systems
- Multipoint and mobile applications
- Wi-Fi access points
- Multiple frequency choices

**✓RoHS 900 MHz Rubber Duck Antennas**

<a href="#">HG903RD-RSP</a>	B	3dBi, Integral Tilt/Swivel RP-SMA Connector	10.99	9.89	8.79	7.69	6.59
<a href="#">HG903RD-SM</a>	B	3dBi, Integral Tilt/Swivel SM Connector	10.99	9.89	8.79	7.69	6.59
<a href="#">HG905RD-RSP</a>	B	5dBi, Integral Tilt/Swivel RP-SMA Connector	19.99	17.99	15.99	13.99	11.99
<a href="#">HG905RD-SM</a>	B	5dBi, Integral Tilt/Swivel SM Connector	19.99	17.99	15.99	13.99	11.99

**✓RoHS 1.9 GHz Rubber Duck Antenna**

<a href="#">HG1903RD-RSP</a>	B	3dBi, Integral Tilt/Swivel RP-SMA Connector	9.99	8.99	7.99	6.99	5.99
------------------------------	---	---	------	------	------	------	------

**✓RoHS 2.4 GHz Rubber Duck Antennas**

<a href="#">HG2401RD-MMCX</a>	C	1dBi, Integral Rt Angle Fixed Mount MMCX Connector	4.99	4.79	4.59	4.24	3.74
<a href="#">HG2401RD-MC</a>	C	1dBi, Integral Rt Angle Fixed Mount MC Connector	2.99	2.96	2.93	2.90	2.87
<a href="#">HG2402RD-RSF</a>	B	2.2dBi, Integral Tilt/Swivel RP-SMA Connector	5.99	5.39	4.79	4.19	3.59
<a href="#">HG2403RD-NM</a>	B	3dBi, Integral Tilt/Swivel NM Connector	7.99	7.19	6.39	5.59	4.79
<a href="#">HG2403RD-RSF</a>	B	3dBi, Integral Tilt/Swivel RP-SMA Connector	7.99	7.19	6.39	5.59	4.79
<a href="#">HG2403RD-RTF</a>	B	3dBi, Integral Tilt/Swivel RP-TNC Connector	7.99	7.19	6.39	5.59	4.79
<a href="#">HG2405RD-NM</a>	B	5dBi, Integral Tilt/Swivel NM Connector	14.99	13.49	11.99	10.49	8.99
<a href="#">HG2405RD-RSP</a>	B	5dBi, Integral Tilt/Swivel RP-SMA Connector	9.99	8.99	7.99	6.99	5.99
<a href="#">HG2405RD-RTP</a>	B	5dBi, Integral Tilt/Swivel RP-TNC Connector	9.99	8.99	7.99	6.99	5.99
<a href="#">HG2407RD-NM</a>	B	7dBi, Integral Tilt/Swivel NM Connector	14.99	13.49	11.99	10.49	8.99
<a href="#">HG2407RD-RSP</a>	B	7dBi, Integral Tilt/Swivel RP-SMA Connector	12.99	11.69	10.39	9.09	7.79
<a href="#">HG2407RD-RTP</a>	B	7dBi, Integral Tilt/Swivel RP-TNC Connector	12.99	11.69	10.39	9.09	7.79
<a href="#">HG2407RD-SM</a>	B	7dBi, Integral Tilt/Swivel SM Connector	14.99	13.49	11.99	10.49	8.99
<a href="#">HG2409RD-NM</a>	B	9dBi, Integral Tilt/Swivel NM Connector	22.99	20.69	18.39	16.09	13.79
<a href="#">HG2409RD-RSP</a>	B	9dBi, Integral Tilt/Swivel RP-SMA Connector	18.99	17.09	15.19	13.29	11.39
<a href="#">HG2409RD-RTP</a>	B	9dBi, Integral Tilt/Swivel RP-TNC Connector	18.99	17.09	15.19	13.29	11.39
<a href="#">HG2409RD-SM</a>	B	9dBi, Integral Tilt/Swivel SM Connector	18.99	17.09	15.19	13.29	11.39

**✓RoHS 3.5 GHz Rubber Duck Antenna**

<a href="#">HG3505RD-RSP</a>	B	5dBi, Integral Tilt/Swivel RP-SMA Connector	14.99	13.49	11.99	10.49	8.99
------------------------------	---	---	-------	-------	-------	-------	------

**✓RoHS 2.4/5.8 GHz Multi-Band Rubber Duck Antennas**

<a href="#">HG2458-5RD-RSP</a>	A	3/5dBi, Integral Tilt/Swivel RP-SMA Connector	16.99	15.29	13.59	11.89	10.19
<a href="#">HG2458RD-RSP</a>	B	3dBi, Integral Tilt/Swivel RP-SMA Connector	12.99	11.69	10.39	9.09	7.79
<a href="#">HG2458RD-SM</a>	B	3dBi, Integral Tilt/Swivel SM Connector	12.99	11.69	10.39	9.09	7.79
<a href="#">HG2458RD-TM</a>	B	3dBi, Integral Tilt/Swivel TM Connector	6.49	6.10	5.71	5.32	4.93

**1.9 GHz, 2.4 GHz Rubber Duck Desktop Mobile Antennas**

L-com's Omnidirectional rubber duck wireless LAN antennas provide broad coverage and 3-9dBi gain. These magnetic mount antennas feature a coaxial sleeve design with an Omnidirectional pattern. These antennas were designed for IEEE 802.11b/g/n wireless LANs and 1.9 GHz cellular PCS radio applications. Mobile applications for these antennas include service vehicles, public transportation, mining vehicles, as well as numerous other commercial and industrial applications where mobility is required. The magnetic base is suitable for affixing to vehicles or other metal surfaces as well as sitting on a tabletop or shelf.

**✓RoHS 1.9 GHz Rubber Duck Antennas with Magnetic Mount**

<a href="#">HG1903MGRD-SM</a>	D	3dBi, 5ft Cable with SM Connector	19.99	19.39	18.79	18.19	CALL
<a href="#">HG1903MGRD-SNP</a>	D	3dBi, 5ft Cable with SMA-Nano Connector	19.99	19.39	18.79	18.19	CALL

**✓RoHS 2.4 GHz Rubber Duck Antennas with Magnetic Mount**

<a href="#">HG2407MGRD-RSP</a>	E	7dBi, 5ft Cable with RP-SMA Connector	19.99	18.99	17.99	16.99	CALL
<a href="#">HG2407MGRD-RTP</a>	E	7dBi, 5ft Cable with RP-TNC Connector	19.99	18.99	17.99	16.99	CALL
<a href="#">HG2409MGRD-RSP</a>	E	9dBi, 5ft Cable with RP-SMA Connector	25.99	24.43	22.87	21.31	19.75
<a href="#">HG2409MGRD-RTP</a>	E	9dBi, 5ft Cable with RP-TNC Connector	25.99	24.43	22.87	21.31	19.75

**✓RoHS 2.4/5.8 GHz Multi-Band Rubber Duck Antennas with Magnetic Mount**

<a href="#">HG2458MGRD-RSP</a>	F	3/5dBi, 5ft Cable with RP-SMA Connector	24.99	23.99	22.99	21.24	18.74
<a href="#">HG2458MGRD-RTP</a>	F	3/5dBi, 5ft Cable with RP-TNC Connector	24.99	23.99	22.99	21.24	18.74

Item #	Code	Description	1-4	5-9	10-24	25+
--------	------	-------------	-----	-----	-------	-----

**900 MHz, 2.4 GHz, 5.4 GHz and 5.8 GHz Sectorial Omnidirectional Array Antennas**

L-com's sector antennas are designed for Cell Site installations and include a variety of gain, frequency and radiation patterns. These Wi-Fi antennas feature our unique heavy-duty mounting systems that allow installation from level to over 20 degrees down-tilt. In addition, 90, 120 and 180 degree arrays are available supporting a wide range of applications. These antennas feature stainless steel construction for all-weather operation.

**✓RoHS 900 MHz Sectorial Array Antennas**

<a href="#">HK913-120</a>	A	13dBi, Multi-Feed, Incl. (3) 120° Antenna with Mounting Array	765.00	726.75	688.50	650.25
<a href="#">HK913-120NF</a>	A	13dBi, Single-Feed, Incl. (3) 120° Antenna with Mounting Array, Splitter, 3 Cables	865.00	821.75	778.50	735.25

"I think the pictures on the web site do a good job of capturing the products. Everything is much easier to find. The check out was pretty smooth. It appeared to be secure and it was pretty streamlined. All in all a "bang up job" on the site." – Nathaniel B. Lyon, Owner, NorthfieldWiFi