




**RoHS Premium Category 6 RJ45 Hi-Speed Network Patch Cords**

Realistic pricing and high quality is what makes L-com's Category 6 patch cords the right choice. Made with high performance 4-pair Category 6 cable and Stewart snagless plugs, these cables are ready to be installed in your network. Affordability and peace of mind are assured when choosing L-com's patch cords. Large volume OEM requests are welcomed with this series. Contact us today for all your patch cord needs.



Ordering is easy, add the desired color code to the part number. Ex: TRD695BLK-1

Item #	Description	Length	1-9	10-24	25-99	100-249	250-499
TRD695__-1	Category 6 Patch Cord, RJ45 / RJ45	1.0 ft	5.99	5.87	5.63	5.27	4.49
TRD695__-3	Category 6 Patch Cord, RJ45 / RJ45	3.0 ft	6.99	6.85	6.57	6.15	5.24
TRD695__-5	Category 6 Patch Cord, RJ45 / RJ45	5.0 ft	7.99	7.83	7.51	7.03	5.99
TRD695__-7	Category 6 Patch Cord, RJ45 / RJ45	7.0 ft	8.99	8.81	8.45	7.91	6.74
TRD695__-10	Category 6 Patch Cord, RJ45 / RJ45	10.0 ft	10.99	10.77	10.33	9.67	8.24
TRD695__-14	Category 6 Patch Cord, RJ45 / RJ45	14.0 ft	12.99	12.73	12.21	11.43	9.74
TRD695__-25	Category 6 Patch Cord, RJ45 / RJ45	25.0 ft	17.99	17.63	16.91	15.83	13.49
TRD695__-50	Category 6 Patch Cord, RJ45 / RJ45	50.0 ft	29.99	29.39	28.19	26.39	22.49
TRD695__-75	Category 6 Patch Cord, RJ45 / RJ45	75.0 ft	41.99	41.15	39.47	36.95	31.49
TRD695__-100	Category 6 Patch Cord, RJ45 / RJ45	100.0 ft	53.99	52.91	50.75	47.51	40.49



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

**RoHS High Performance Category 6 Staggered Alignment Plugs with Loading Bars**

This staggered alignment plug will accommodate typical 24 gauge solid or stranded cable. Fully compatible with Category 6 applications. They are specially designed with a multi-level contact configuration and loading bars for precise control of pairing arrangement. This controls the distance between critical pairs that provide lower levels of crosstalk and higher performance. Sold only in packages of 50 plugs.

TSP4288C6	Modular Plugs, RJ45(8x8) Category 6, Pkg/50	49.95	45.95	41.96	37.96	CALL
-----------	---	-------	-------	-------	-------	------

**RoHS Premium Panel Mounted Modular Coupler Kits - Shielded and Unshielded Category 6**

These unique coupler kits allow panel mounting in virtually any panel thickness. A solid die-cast metal mounting frame provides secure mounting and reliable grounding. Kits include a snap-in coupler, mounting frame and two 4-40 machine screws.


ECF504-C6	Category 6 Unshielded RJ45 (8x8) Deluxe Panel Coupler Kit	11.95	10.99	10.04	9.08	8.13
ECF504-SC6	Category 6 Shielded RJ45 (8x8) Deluxe Panel Coupler Kit	13.95	12.83	11.72	10.60	9.49

**RoHS RJ45 (8x8) Keystone Feed-thru Couplers - Shielded and Unshielded Category 6**


These couplers utilize two RJ45 (8x8) modular jacks and fit into a standard keystone style opening. A slim housing design permits high density mounting. Couplers listed include 6 performance ratings in shielded and unshielded versions. Connector housings enclosed within a fully stamped shielding. Designed to work with EIA/TIA 568A and B wiring.

TDG1026KC6	Category 6 Unshielded RJ45 (8x8) Keystone Feed-thru Coupler	9.95	8.96	7.96	6.97	5.97
TDG1026KS-C6	Category 6 Shielded RJ45 (8x8) Keystone Feed-thru Coupler	12.95	11.66	10.36	9.07	7.77

**Easily install a premium ECF coupler kit**



Secure frame in specified opening with supplied hardware and align coupler in proper orientation to the opening.



Seat bottom retainer and pivot coupler upward while depressing upper retainer.



Coupler fully seated.

