



Item #	Description	1-9	10-24	25-99	100-249	250-499
✓RoHS WT6788D	Ruggedized IP67 Rated RJ45 Ethernet Plug Kit Installing Ethernet in harsh environments has never been easier. This IP67 rated plug housing is available for use with either shielded or non-shielded connections. A gasket seal keeps out unwanted contaminants and moisture. The optional flexible strain relief controls the bend radius of the cable. Call today to discuss your application with us!					
WT6788D	Non-Shielded Dome Style	19.95	19.15	18.35	17.56	16.76
WT6788F	Non-Shielded Flex Style	19.95	19.15	18.35	17.56	16.76
WT6788DS	Shielded Dome Style	22.95	22.03	21.11	20.20	19.28
WT6788FS	Shielded Flex Style	22.95	22.03	21.11	20.20	19.28
TSP4088C5	Replacement RJ45 Non-Shielded Plugs, Pkg/50	29.95	27.55	25.16	22.76	CALL
TSP4088C5S	Replacement RJ45 Shielded Plugs, Pkg/50	49.95	45.95	41.96	37.96	CALL
✓RoHS WT6788DS	Ruggedized IP67 Rated Keystone Flange Adapter Kits Pass your Ethernet connections through a panel while still maintaining an IP67 rated seal. These receptacle kits consist of an IP67 rated flange adapter and industry standard keystone jacks and couplers. Don't see the combination you need? Call today and we'll help you find the right connection system for your application.					
WT6700FM	Front Mount Empty	17.95	17.23	16.51	15.80	15.08
WT6700RM	Rear Mount Empty	17.95	17.23	16.51	15.80	15.08
WT67KCSF	Front Mount C5E Coupler	24.95	23.95	22.95	21.96	20.96
WT67KCSR	Rear Mount C5E Coupler	24.95	23.95	22.95	21.96	20.96
WT671105FM	Front Mount C5E IDC 110 Jack	19.95	19.15	18.35	17.56	16.76
WT671105RM	Rear Mount C5E IDC 110 Jack	19.95	19.15	18.35	17.56	16.76
✓RoHS WT6788F	Protective Covers for WT67 Series Plugs and Jacks Maintain the IP67 rating for all open plugs and jacks with these covers. These caps are specifically designed to fit the WT67 series jacks and plugs. When a cable is connected, just attach a cap over the expose connection and the seal is maintained.					
WT67RC	IP67 Jack Cover for Female Receptacles	5.95	5.71	5.47	5.24	5.00
WT67RCT	IP67 Jack Cover for Female Receptacles with Tether	10.95	10.51	10.07	9.64	9.20
WT67PC	IP67 Jack Cover for Male Plug Kits	6.95	6.67	6.39	6.12	5.84
WT67PCT	IP67 Jack Cover for Male Plug Kits with Tether	8.95	8.59	8.23	7.88	7.52

Item #	Description	1-9	10-24	25-99	100-249	250-499
✓RoHS WT67RC	Protective Covers for WT67 Series Plugs and Jacks Maintain the IP67 rating for all open plugs and jacks with these covers. These caps are specifically designed to fit the WT67 series jacks and plugs. When a cable is connected, just attach a cap over the expose connection and the seal is maintained.					
WT67RC	IP67 Jack Cover for Female Receptacles	5.95	5.71	5.47	5.24	5.00
WT67RCT	IP67 Jack Cover for Female Receptacles with Tether	10.95	10.51	10.07	9.64	9.20
WT67PC	IP67 Jack Cover for Male Plug Kits	6.95	6.67	6.39	6.12	5.84
WT67PCT	IP67 Jack Cover for Male Plug Kits with Tether	8.95	8.59	8.23	7.88	7.52

Tip

Easily attach a field installable plug

STEP 1

Slide compression nut, coupling and plug housing onto cable.

STEP 2

Strip & prepare conductors for crimping. Trim to .56"

STEP 3

Install plug and crimp.

STEP 4

Slide crimped connector into place and tighten compression nut.

Industrial Category 5E Field Installable Connectors (Exploded View)

<p>Compact Dome Cable Entry</p>	<p>Available with Shielded or Non-Shielded Plug</p>	<p>Flexible Cable Entry</p>	<p>Available with Shielded or Non-Shielded Plug</p>
<p>Quick Latching Housing</p>	<p>Gasket Seal for IP67 Rating</p>	<p>Quick Latching Housing</p>	<p>Gasket Seal for IP67 Rating</p>

"We have ordered many of your products recently, and have been very pleased with the quality of the products, and the availability and delivery of the products. Keep up the good work." - Brad Risinger, Advisory Optical Engineer, Northrup Grumman Corporation