



Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
<b>✓RoHS Deluxe Panel Mounted Modular Couplers, 30 Microinches Gold, Ivory Color</b>							
These straight and cross wired modular couplers are available exclusively from L-com. Eight different configurations all fit into the same 0.675 x 0.900 inch rectangular opening. Wire contacts have 30 microinch gold plating for multiple insertions. Plastic is 94V-0 rated. Color: Ivory. Flange accepts #4 or #5 mounting screws to be purchased separately. Category 3 rated.							
<a href="#">ECF504-4C</a>	Modular Coupler, RJ11 (6x4), Crossed, 30µ	Ivory	3.75	3.68	3.53	3.30	2.81
<a href="#">ECF504-6C</a>	Modular Coupler, RJ12 (6x6), Crossed, 30µ	Ivory	3.95	3.87	3.71	3.48	2.96
<a href="#">ECF504-6CMJ</a>	Modular Coupler, MMJ (6x6), Crossed, 30µ	Ivory	3.95	3.87	3.71	3.48	2.96
<a href="#">ECF504-8C</a>	Modular Coupler, RJ45 (8x8), Crossed, 30µ	Ivory	4.95	4.85	4.65	4.36	3.71
<a href="#">ECF504-4S</a>	Modular Coupler, RJ11 (6x4), Straight, 30µ	Ivory	3.75	3.68	3.53	3.30	2.81
<a href="#">ECF504-6S</a>	Modular Coupler, RJ12 (6x6), Straight, 30µ	Ivory	3.95	3.87	3.71	3.48	2.96
<a href="#">ECF504-6SMJ</a>	Modular Coupler, MMJ (6x6), Straight, 30µ	Ivory	3.95	3.87	3.71	3.48	2.96
<a href="#">ECF504-8SK</a>	Modular Coupler, RJ45 (8x8), Straight, 30µ	Ivory	4.95	4.85	4.65	4.36	3.71
<a href="#">ECF440</a>	Machine Screws, 4-40 x 5/16", Pkg/100		4.35	4.00	3.65	3.31	2.96

<b>✓RoHS Deluxe Panel Mounted Modular Jacks - 10" Wire Leads, 30 Microinches Gold, Ivory Color</b>							
One difficulty in using modular jacks is the mounting problem on a panel. L-com's solution to this problem is providing a flange that mounts with two screws in a 0.675" x 0.900" rectangular opening. Choice of RJ11/12 (6x6) or RJ45 (8x8K) usable with keyed or non-keyed plugs. Custom versions of other jack types considered in quantities of 500/up. Mounting screws must be purchased separately.							
<a href="#">ECJ504-6</a>	Modular Panel Jack, RJ12 (6x6) / Wires, 30µ	Ivory	3.95	3.87	3.71	3.48	2.96
<a href="#">ECJ504-8</a>	Modular Panel Jack, RJ45K (8x8K) / Wires, 30µ	Ivory	4.29	4.20	4.03	3.78	3.22
<a href="#">ECF440</a>	Machine Screws, 4-40 x 5/16", Pkg/100		4.35	4.00	3.65	3.31	2.96

<b>✓RoHS Deluxe Panel Mounted Couplers, 50 Microinches Gold, Black Color</b>							
These couplers are similar to the ECF504 Series with two changes. The molding has been changed to a Black color for applications when Ivory is not wanted. Also, the contacts have 50 microinches of gold for superior mating with modular plugs. Mounting screws must be purchased separately. Category 3 rated.							
<a href="#">ECF504B-4S</a>	Modular Coupler, RJ11 (6x4), Straight, 50µ	Black	3.75	3.68	3.53	3.30	2.81
<a href="#">ECF504B-6S</a>	Modular Coupler, RJ12 (6x6), Straight, 50µ	Black	3.95	3.87	3.71	3.48	2.96
<a href="#">ECF504B-8SK</a>	Modular Coupler, RJ45K (8x8K), Straight, 50µ	Black	4.95	4.85	4.65	4.36	3.71
<a href="#">ECF440</a>	Machine Screws, 4-40 x 5/16", Pkg/100		4.35	4.00	3.65	3.31	2.96

<b>✓RoHS 19" Patch Panels - Equipped with 16 or 32 ECF504 Series Modular Couplers</b>							
These 19" patch panels utilize the ECF504 series couplers. For your convenience, two panel heights are offered; 1.75" with 16 modular adapters or 3.5" with 32 modular adapters. Panel legend is 1-16 or 1-32. Color: Bone. Available with straight-thru wiring.							
<a href="#">PR175F504-6S</a>	1.75" 16 Port Panel RJ12 (6x6), Straight-Thru	Bone	79.95	73.55	67.16	60.76	CALL
<a href="#">PR175F504-8SK</a>	1.75" 16 Port Panel RJ45 (8x8), Straight, Keyed	Bone	89.95	82.75	75.56	68.36	CALL
<a href="#">PR35F504-6S</a>	3.50" 32 Port Panel RJ12 (6x6), Straight-Thru	Bone	119.95	110.35	100.76	91.16	CALL
<a href="#">PR35F504-8SK</a>	3.50" 32 Port Panel RJ45 (8x8), Straight, Keyed	Bone	139.95	128.75	117.56	106.36	CALL

<b>✓RoHS 19" Modular Patch Panels - Equipped with 16 or 32 ECF504B Modular Couplers</b>							
These panels utilize the ECF504B couplers with 50 microinch plating. 16 and 32 port available. Straight thru pinned only. Color: Black.							
<a href="#">PR175F504B-4S</a>	1.75" 16 Port Panel RJ11 (6x4), Straight-Thru	Black	69.95	64.35	58.76	53.16	CALL
<a href="#">PR175F504B-6S</a>	1.75" 16 Port Panel RJ12 (6x6), Straight-Thru	Black	79.95	73.55	67.16	60.76	CALL
<a href="#">PR175F504B-8SK</a>	1.75" 16 Port Panel RJ45 (8x8), Straight, Keyed	Black	89.95	82.75	75.56	68.36	CALL
<a href="#">PR35F504B-4S</a>	3.50" 32 Port Panel RJ11 (6x4), Straight-Thru	Black	129.95	119.55	109.16	98.76	CALL
<a href="#">PR35F504B-6S</a>	3.50" 32 Port Panel RJ12 (6x6), Straight-Thru	Black	139.95	128.75	117.56	106.36	CALL
<a href="#">PR35F504B-8SK</a>	3.50" 32 Port Panel RJ45 (8x8), Straight, Keyed	Black	169.95	156.35	142.76	129.16	CALL

### How Rack Spaces and Sizes are Measured

1 Rack Space = 1.75 inches

2 Rack Spaces = 3.5 inches

Racks are a great way to neaten up wiring closets and labs. Network equipment and rack panels usually come in 1.75", 3.5" and 5.25" heights. (1, 2 and 3 rack spaces).

