

Item #	Description	1-9	10-24	25-99	100-249	250-499
✓RoHS SDG450XS	ne Gender Changer/Adapters - Reduce Port Receptacle Strain Up To 90%					
DGB9F	Slim-Line Gender Changer, DB9 Female / Female	4.95	4.46	3.96	3.47	2.97
DGB9M	Slim-Line Gender Changer, DB9 Male / Male	4.95	4.46	3.96	3.47	2.97
DGB15F	Slim-Line Gender Changer, DB15 Female / Female	5.95	5.36	4.76	4.17	3.57
DGB15M	Slim-Line Gender Changer, DB15 Male / Male	5.95	5.36	4.76	4.17	3.57
DGB25F	Slim-Line Gender Changer, DB25 Female / Female	6.95	6.26	5.56	4.87	4.17
DGB25M	Slim-Line Gender Changer, DB25 Male / Male	6.95	6.26	5.56	4.87	4.17
DGB37F	Slim-Line Gender Changer, DB37 Female / Female	8.95	8.06	7.16	6.26	5.37
DGB37M	Slim-Line Gender Changer, DB37 Male / Male	8.95	8.06	7.16	6.26	5.37
DGB50F	Slim-Line Gender Changer, DB50 Female / Female	10.95	9.86	8.76	7.66	6.57
DGB50M	Slim-Line Gender Changer, DB50 Male / Male	10.95	9.86	8.76	7.66	6.57

✓RoHS	Socket Saver Adapters - Extend D-Sub Connector Usage and Avoid Major Repairs					
DGB9MF	Slim-Line Socket Saver, DB9 Male / Female	4.95	4.46	3.96	3.47	2.97
DGB15MF	Slim-Line Socket Saver, DB15 Male / Female	5.95	5.36	4.76	4.17	3.57
DGB25MF	Slim-Line Socket Saver, DB25 Male / Female	6.95	6.26	5.56	4.87	4.17
DGB37MF	Slim-Line Socket Saver, DB37 Male / Female	8.95	8.06	7.16	6.26	5.37
DGB50MF	Slim-Line Socket Saver, DB50 Male / Female	10.95	9.86	8.76	7.66	6.57

✓RoHS	High-Density Slim-Line Gender Changers - Same Small Size for High-Density D-Subs					
DGBH15F	Slim-Line Gender Changer, HD15 Female / Female	7.95	7.16	6.36	5.57	4.77
DGBH15M	Slim-Line Gender Changer, HD15 Male / Male	7.95	7.16	6.36	5.57	4.77
DGBH26F	Slim-Line Gender Changer, HD26 Female / Female	8.95	8.06	7.16	6.26	5.37
DGBH26M	Slim-Line Gender Changer, HD26 Male / Male	8.95	8.06	7.16	6.26	5.37
DGBH44F	Slim-Line Gender Changer, HD44 Female / Female	9.95	8.96	7.96	6.96	5.97
DGBH44M	Slim-Line Gender Changer, HD44 Male / Male	9.95	8.96	7.96	6.96	5.97
DGBH62F	Slim-Line Gender Changer, HD62 Female / Female	12.95	11.66	10.36	9.07	7.77
DGBH62M	Slim-Line Gender Changer, HD62 Male / Male	12.95	11.66	10.36	9.07	7.77
DGBH78F	Slim-Line Gender Changer, HD78 Female / Female	13.95	12.56	11.16	9.76	8.37
DGBH78M	Slim-Line Gender Changer, HD78 Male / Male	13.95	12.56	11.16	9.76	8.37

✓RoHS	High-Density Socket Saver Adapters - Great for Preventing Wear on High-Density Connectors					
DGBH15MF	Slim-Line Socket Saver, HD15 Male / Female	7.95	7.16	6.36	5.57	4.77
DGBH26MF	Slim-Line Socket Saver, HD26 Male / Female	8.95	8.06	7.16	6.26	5.37
DGBH44MF	Slim-Line Socket Saver, HD44 Male / Female	9.95	8.96	7.96	6.96	5.97
DGBH62MF	Slim-Line Socket Saver, HD62 Male / Female	12.95	11.66	10.36	9.07	7.77
DGBH78MF	Slim-Line Socket Saver, HD78 Male / Female	13.95	12.56	11.16	9.76	8.37


✓RoHS	Slim-Line Gender Changer/Adapters - with Pin 9 Missing for Legacy VGA Cable Applications					
DGBV15F	Slim-Line Gender Changer, HD15 Female / Female	7.95	7.16	6.36	5.57	4.77
DGBV15M	Slim-Line Gender Changer, HD15 Male / Male	7.95	7.16	6.36	5.57	4.77
DGBV15MF	Slim-Line Socket Saver, HD15 Male / Female	7.95	7.16	6.36	5.57	4.77
DMA100M	PS-2 Monitor Adapter, DB9 Male / HD15 Male	7.55	6.80	6.04	5.28	4.53

✓RoHS	Slim-Line Gender Changers and Socket Saver - Typical Centronic 36 and SCSI/Telco 50					
DGC36F	Slim-Line Centronic Gender Changer, 36 Pin Female / Female	9.65	8.69	7.72	6.76	5.79
DGC36M	Slim-Line Centronic Gender Changer, 36 Pin Male / Male	9.65	8.69	7.72	6.76	5.79
DGC50F	Slim-Line SCSI Gender Changer, 50 Pin Female / Female	10.95	9.86	8.76	7.66	6.57
DGC50M	Slim-Line SCSI Gender Changer, 50 Pin Male / Male	10.95	9.86	8.76	7.66	6.57
DGC50MF	Slim-Line SCSI Socket Saver, 50 Pin Male / Female	10.95	9.86	8.76	7.66	6.57

✓RoHS DB9, HD15, DB15 and DB25 Low Profile Right Angle Adapters - Molded and Fully Shielded

Connecting cables in tight spaces can be a problem in many applications. These low profile adapters solve this problem by allowing cables to be connected at a 90 degree angle. Two versions are available for each connector size allowing for cables to exit in opposite directions. Adapters are male to female, fully shielded and are overmolded with Gray PVC. Mating hardware is reversible allowing for use in virtually any application. See [page 70](#) for cable exit detail.

DG909MF1	Low Profile Right Angle Adapter, DB9 Male / Female, Cable Exit 1	7.00	6.58	6.16	5.74	5.32
DG909MF2	Low Profile Right Angle Adapter, DB9 Male / Female, Cable Exit 2	7.00	6.58	6.16	5.74	5.32
DG9015MF1	Low Profile Right Angle Adapter, DB15 Male / Female, Cable Exit 1	8.00	7.52	7.04	6.56	6.08
DG9015MF2	Low Profile Right Angle Adapter, DB15 Male / Female, Cable Exit 2	8.00	7.52	7.04	6.56	6.08
DG90H15MF1	Low Profile Right Angle Adapter, HD15 Male / Female, Cable Exit 1	8.00	7.52	7.04	6.56	6.08
DG90H15MF2	Low Profile Right Angle Adapter, HD15 Male / Female, Cable Exit 2	8.00	7.52	7.04	6.56	6.08
DG9025MF1	Low Profile Right Angle Adapter, DB25 Male / Female, Cable Exit 1	10.00	9.40	8.80	8.20	7.60
DG9025MF2	Low Profile Right Angle Adapter, DB25 Male / Female, Cable Exit 2	10.00	9.40	8.80	8.20	7.60



Easily panel mount adapters **See The Video**
www.l-com.com/Videos/A03

STEP 1

1. Remove standard hardware provided with adapter. Mount adapter from rear of panel.

STEP 2

2. Secure with jackscrew SDG450XS (purchased separately) from front of panel.

STEP 3

3. Thread hex nut SDHS (purchased separately) onto exposed threads of SDG450XS.

***Note:** Maximum recommended panel thickness is 0.062". Dimensions in excess of 0.062" can limit proper cable mating due to hex nut protrusion. Panels that exceed 0.062" can be milled down to the recommended thickness in the area around the adapter.

How to panel mount adapters
 See the free video tip and more at L-com.com/Videos/A03