




**Tip** What is S-Video (S-VHS)?

The term S-Video is derived from the way the video signal is transmitted. In S-Video the signal is separated into two components hence the term Separate Video or S-Video. Two 75 Ohm coaxial cables and a Mini DIN 4 connector are utilized to transmit the two component signals. One of the coaxial cables carries the Luminance Signal (brightness or Y component) while the second 75 Ohm coaxial cable carries the Chrominance Signal (color or C component). By separating the video signal into two components a better quality picture is produced than composite video that utilizes one coaxial cable to transmit both signals. The term S-VHS is an acronym for Super-Video Home System.



Item #	Description	1-9	10-24	25-99	100-249	250-499
<b>Molded S-Video Cable Assemblies, 75 Ohm Dual Coaxial in Single Jacket</b>						
<a href="#">CCD234MM-1</a>	Molded Mini DIN 4 Male / Male, 1.0 ft	5.50	5.17	4.84	4.51	4.18
<a href="#">CCD234MM-2</a>	Molded Mini DIN 4 Male / Male, 2.0 ft	6.20	5.83	5.46	5.08	4.71
<a href="#">CCD234MM-3</a>	Molded Mini DIN 4 Male / Male, 3.0 ft	6.90	6.49	6.07	5.66	5.24
<a href="#">CCD234MM-5</a>	Molded Mini DIN 4 Male / Male, 5.0 ft	8.30	7.80	7.30	6.81	6.31
<a href="#">CCD234MM-7.5</a>	Molded Mini DIN 4 Male / Male, 7.5 ft	10.05	9.45	8.84	8.24	7.64
<a href="#">CCD234MM-10</a>	Molded Mini DIN 4 Male / Male, 10.0 ft	11.80	11.09	10.38	9.68	8.97
<a href="#">CCD234MM-20</a>	Molded Mini DIN 4 Male / Male, 20.0 ft	18.80	17.67	16.54	15.42	14.29
<a href="#">CCD234MM-30</a>	Molded Mini DIN 4 Male / Male, 30.0 ft	25.80	24.25	22.70	21.16	19.61
<a href="#">CCD234MM-40</a>	Molded Mini DIN 4 Male / Male, 40.0 ft	32.80	30.83	28.86	26.90	24.93
<a href="#">CCD234MM-50</a>	Molded Mini DIN 4 Male / Male, 50.0 ft	39.80	37.41	35.02	32.64	30.25
<a href="#">CCD234MF-1</a>	Molded Mini DIN 4 Male / Female, 1.0 ft	5.50	5.17	4.84	4.51	4.18
<a href="#">CCD234MF-2</a>	Molded Mini DIN 4 Male / Female, 2.0 ft	6.20	5.83	5.46	5.08	4.71
<a href="#">CCD234MF-3</a>	Molded Mini DIN 4 Male / Female, 3.0 ft	6.90	6.49	6.07	5.66	5.24
<a href="#">CCD234MF-5</a>	Molded Mini DIN 4 Male / Female, 5.0 ft	8.30	7.80	7.30	6.81	6.31
<a href="#">CCD234MF-7.5</a>	Molded Mini DIN 4 Male / Female, 7.5 ft	10.05	9.45	8.84	8.24	7.64
<a href="#">CCD234MF-10</a>	Molded Mini DIN 4 Male / Female, 10.0 ft	11.80	11.09	10.38	9.68	8.97
<a href="#">CCD234MF-20</a>	Molded Mini DIN 4 Male / Female, 20.0 ft	18.80	17.67	16.54	15.42	14.29
<b>Assembled S-Video Cable Assemblies, 75 Ohm Dual Coaxial in Single Jacket</b>						
<a href="#">CCD244MM-1</a>	Assembled Mini DIN 4 Male / Male, 1.0 ft	13.50	12.69	11.88	11.07	10.26
<a href="#">CCD244MM-2</a>	Assembled Mini DIN 4 Male / Male, 2.0 ft	14.20	13.35	12.50	11.64	10.79
<a href="#">CCD244MM-3</a>	Assembled Mini DIN 4 Male / Male, 3.0 ft	14.90	14.01	13.11	12.22	11.32
<a href="#">CCD244MM-5</a>	Assembled Mini DIN 4 Male / Male, 5.0 ft	16.30	15.32	14.34	13.37	12.39
<a href="#">CCD244MM-7.5</a>	Assembled Mini DIN 4 Male / Male, 7.5 ft	18.05	16.97	15.88	14.80	13.72
<a href="#">CCD244MM-10</a>	Assembled Mini DIN 4 Male / Male, 10.0 ft	19.80	18.61	17.42	16.24	15.05
<a href="#">CCD244MM-20</a>	Assembled Mini DIN 4 Male / Male, 20.0 ft	26.80	25.19	23.58	21.98	20.37
<a href="#">CCD244MF-1</a>	Assembled Mini DIN 4 Male / Female, 1.0 ft	13.50	12.69	11.88	11.07	10.26
<a href="#">CCD244MF-2</a>	Assembled Mini DIN 4 Male / Female, 2.0 ft	14.20	13.35	12.50	11.64	10.79
<a href="#">CCD244MF-3</a>	Assembled Mini DIN 4 Male / Female, 3.0 ft	14.90	14.01	13.11	12.22	11.32
<a href="#">CCD244MF-5</a>	Assembled Mini DIN 4 Male / Female, 5.0 ft	16.30	15.32	14.34	13.37	12.39
<a href="#">CCD244MF-7.5</a>	Assembled Mini DIN 4 Male / Female, 7.5 ft	18.05	16.97	15.88	14.80	13.72
<a href="#">CCD244MF-10</a>	Assembled Mini DIN 4 Male / Female, 10.0 ft	19.80	18.61	17.42	16.24	15.05
<a href="#">CCD244MF-20</a>	Assembled Mini DIN 4 Male / Female, 20.0 ft	26.80	25.19	23.58	21.98	20.37
<b>Assembled S-Video Cable Assemblies - Molded Dual RCA-M, 75 Ohm Dual Coaxial Breakout Cable</b>						
<a href="#">CCD244MR-1</a>	Assembled Mini DIN 4 Male / Dual RCA Male, 1.0 ft	9.55	8.60	7.64	6.69	5.73
<a href="#">CCD244MR-2</a>	Assembled Mini DIN 4 Male / Dual RCA Male, 2.0 ft	10.35	9.32	8.28	7.24	6.21
<a href="#">CCD244MR-3</a>	Assembled Mini DIN 4 Male / Dual RCA Male, 3.0 ft	11.15	10.04	8.92	7.81	6.69
<a href="#">CCD244MR-5</a>	Assembled Mini DIN 4 Male / Dual RCA Male, 5.0 ft	12.75	11.48	10.20	8.92	7.65
<a href="#">CCD244MR-7.5</a>	Assembled Mini DIN 4 Male / Dual RCA Male, 7.5 ft	14.75	13.28	11.80	10.33	8.85
<a href="#">CCD244MR-10</a>	Assembled Mini DIN 4 Male / Dual RCA Male, 10.0 ft	16.75	15.08	13.40	11.73	10.05
<a href="#">CCD244MR-20</a>	Assembled Mini DIN 4 Male / Dual RCA Male, 20.0 ft	24.75	22.28	19.80	17.33	14.85
<b>Assembled S-Video Cable Assemblies - Molded Dual BNC-M, 75 Ohm Dual Coaxial Breakout Cable</b>						
<a href="#">CCD244MB-1</a>	Assembled Mini DIN 4 Male / Dual BNC Male, 1.0 ft	13.50	12.69	11.88	11.07	10.26
<a href="#">CCD244MB-2</a>	Assembled Mini DIN 4 Male / Dual BNC Male, 2.0 ft	14.20	13.35	12.50	11.64	10.79
<a href="#">CCD244MB-3</a>	Assembled Mini DIN 4 Male / Dual BNC Male, 3.0 ft	14.90	14.01	13.11	12.22	11.32
<a href="#">CCD244MB-5</a>	Assembled Mini DIN 4 Male / Dual BNC Male, 5.0 ft	16.30	15.32	14.34	13.37	12.39
<a href="#">CCD244MB-7.5</a>	Assembled Mini DIN 4 Male / Dual BNC Male, 7.5 ft	18.05	16.97	15.88	14.80	13.72
<a href="#">CCD244MB-10</a>	Assembled Mini DIN 4 Male / Dual BNC Male, 10.0 ft	19.80	18.61	17.42	16.24	15.05
<a href="#">CCD244MB-20</a>	Assembled Mini DIN 4 Male / Dual BNC Male, 20.0 ft	26.80	25.19	23.58	21.98	20.37
<b>Assembled S-Video to Single Composite RCA Cable Assemblies</b>						
These cables combine the S-Video Mini DIN 4 connector found on SVHS with the single RCA connector used for composite video allowing the conversion from S-Video transmission to composite video.						
<a href="#">CCD144MR-2</a>	Assembled Mini DIN 4 Male / Single RCA Male, 2.0 ft	11.00	10.34	9.68	9.02	8.36
<a href="#">CCD144MR-6</a>	Assembled Mini DIN 4 Male / Single RCA Male, 6.0 ft	13.00	12.22	11.44	10.66	9.88
<a href="#">CCD144MR-10</a>	Assembled Mini DIN 4 Male / Single RCA Male, 10.0 ft	15.00	14.10	13.20	12.30	11.40
<a href="#">CCD144MR-15</a>	Assembled Mini DIN 4 Male / Single RCA Male, 15.0 ft	17.50	16.45	15.40	14.35	13.30
<a href="#">CCD144MR-20</a>	Assembled Mini DIN 4 Male / Single RCA Male, 20.0 ft	20.00	18.80	17.60	16.40	15.20
<a href="#">CCD144MR-25</a>	Assembled Mini DIN 4 Male / Single RCA Male, 25.0 ft	22.50	21.15	19.80	18.45	17.10