

LOW-LOSS CABLES



CA4RNPMM002



CA4RTMRTF020



CA4NMRTP020

Item #	Description	1-9	10-24	25-99	100-249	250-499
RoHS 400-Series Coaxial Assemblies						
CA4N002	N-Male to N-Female, 2ft	22.99	20.69	18.39	16.09	13.79
CA4N020	N-Male to N-Female, 20ft	32.99	29.69	26.39	23.09	19.79
CA4N025	N-Male to N-Female, 25ft	39.99	35.99	31.99	27.99	23.99
CA4N050	N-Male to N-Female, 50ft	49.99	44.99	39.99	34.99	29.99
CA4N075	N-Male to N-Female, 75ft	87.99	79.19	70.39	61.59	52.79
CA3N020	N-Male to N-Male, 20ft	29.99	26.99	23.99	20.99	17.99
CA3N025	N-Male to N-Male, 25ft	34.99	31.49	27.99	24.49	20.99
CA3N030	N-Male to N-Male, 30ft	54.99	49.49	43.99	38.49	32.99
CA3N040	N-Male to N-Male, 40ft	64.99	58.49	51.99	45.49	38.99
CA3N050	N-Male to N-Male, 50ft	47.99	43.19	38.39	33.59	28.79
CA3N075	N-Male to N-Male, 75ft	87.99	79.19	70.39	61.59	52.79
CA4RNPNM002	RP N Plug to N-Male, 2ft	21.99	19.79	17.59	15.39	13.19
CA4RNPNM075	RP N Plug to RP N Plug, 75ft	89.99	82.79	75.59	68.39	61.19
CA4NMRSF020	RP-SMA Plug to N-Male, 20ft	34.99	31.49	27.99	24.49	20.99
CA4NMRSF025	RP-SMA Plug to N-Male, 25ft	39.99	35.99	31.99	27.99	23.99
CA4NMRSF030	RP-SMA Plug to N-Male, 30ft	44.99	40.49	35.99	31.49	26.99
CA4NMRSF050	RP-SMA Plug to N-Male, 50ft	49.99	44.99	39.99	34.99	29.99
CA4NMRSF075	RP-SMA Plug to N-Male, 75ft	87.99	79.19	70.39	61.59	52.79
CA4RTMRTF002	RP-TNC Jack to RP-TNC Plug, 2ft	21.99	19.79	17.59	15.39	13.19
CA4RTMRTF020	RP-TNC Jack to RP-TNC Plug, 20ft	44.99	40.49	35.99	31.49	26.99
CA4RTMRTF025	RP-TNC Jack to RP-TNC Plug, 25ft	49.99	44.99	39.99	34.99	29.99
CA4RTMRTF050	RP-TNC Jack to RP-TNC Plug, 50ft	69.99	62.99	55.99	48.99	41.99
CA4NMRTP020	RP-TNC Plug to N-Male, 20ft	39.99	35.99	31.99	27.99	23.99
CA4NMRTP025	RP-TNC Plug to N-Male, 25ft	39.99	35.99	31.99	27.99	23.99
CA4NMRTP050	RP-TNC Plug to N-Male, 50ft	49.99	44.99	39.99	34.99	29.99
CA4NMRTP075	RP-TNC Plug to N-Male, 75ft	84.99	78.19	71.39	64.59	57.79
CA4RTPRTP002	RP-TNC Plug to RP-TNC Plug, 2ft	21.99	19.79	17.59	15.39	13.19
CA4RTPRTP050	RP-TNC Plug to RP-TNC Plug, 50ft	44.99	43.19	41.39	38.24	33.74
CA4NMSM002	SMA Male to N-Male, 2ft	24.99	22.49	19.99	17.49	14.99
CA4NMSM025	SMA Male to N-Male, 25ft	49.99	44.99	39.99	34.99	29.99
RoHS 600-Series Coaxial Assemblies						
CA-6NMNM010	N-Male to N-Male, 10ft	52.00	46.80	41.60	36.40	31.20
CA-6NMNM025	N-Male to N-Male, 25ft	70.00	63.00	56.00	49.00	42.00
CA-6NMNM050	N-Male to N-Male, 50ft	100.00	92.00	84.00	76.00	68.00
CA-6NMNM075	N-Male to N-Male, 75ft	130.00	123.50	117.00	110.50	CALL
CA-6NMNM100	N-Male to N-Male, 100ft	160.00	152.00	144.00	136.00	CALL
RoHS 900-Series Coaxial Assemblies						
CC-9NMNF025	N-Male to N-Female, 25ft	556.00	500.40	444.80	389.20	CALL
CC-9NMNF050	N-Male to N-Female, 50ft	798.00	718.20	638.40	558.60	CALL
CC-9NMNF075	N-Male to N-Female, 75ft	1220.00	1098.00	976.00	854.00	CALL
CC-9NMNF100	N-Male to N-Female, 100ft	1550.00	1395.00	1240.00	1085.00	CALL
CC-9NMNM025	N-Male to N-Male, 25ft	556.00	500.40	444.80	389.20	CALL
CC-9NMNM050	N-Male to N-Male, 50ft	798.00	718.20	638.40	558.60	CALL
CC-9NMNM075	N-Male to N-Male, 75ft	1220.00	1098.00	976.00	854.00	CALL
CC-9NMNM100	N-Male to N-Male, 100ft	1550.00	1395.00	1240.00	1085.00	CALL

Attenuation and Avg. Power (20°C) Chart

100-Series Coaxial Cable			400-Series Coaxial Cable		
Frequency (MHz)	Attenuation dB (100m / 100ft)	Avg. Power (KW)	Frequency (MHz)	Attenuation dB (100m / 100ft)	Avg. Power (KW)
900	74.80 / 22.80	0.05	900	12.8 / 3.9	0.58
1800	108.79 / 33.16	0.03	1800	18.6 / 5.67	0.40
2500	130.58 / 39.80	0.01	2500	22.2 / 6.8	0.33
195-Series Coaxial Cable			5800	35.5 / 10.8	0.21
Frequency (MHz)	Attenuation dB (100m / 100ft)	Avg. Power (KW)	600-Series Coaxial Cable		
900	36.5 / 1.11	0.15	Frequency (MHz)	Attenuation dB (100m / 100ft)	Avg. Power (KW)
1800	52.5 / 16.0	0.11	900	8.2 / 2.5	0.93
2500	62.4 / 19.0	0.09	1800	12.1 / 3.7	0.63
5800	98.1 / 29.9	0.06	2500	14.5 / 4.4	0.52
200-Series Coaxial Cable			5800	23.8 / 7.3	0.32
Frequency (MHz)	Attenuation dB (100m / 100ft)	Avg. Power (KW)	900-Series Coaxial Cable		
900	32.6 / 9.9	0.16	Frequency (MHz)	Attenuation dB (100m / 100ft)	Avg. Power (KW)
1800	46.6 / 14.2	0.11	900	1.70 / 5.6	1.5
2500	55.4 / 16.9	0.10	1800	2.48 / 8.2	1.0
5800	86.5 / 26.4	0.06	2500	2.98 / 9.8	0.9
240-Series Coaxial Cable			5800	4.90 / 16.0	0.52
Frequency (MHz)	Attenuation dB (100m / 100ft)	Avg. Power (KW)			
900	24.8 / 7.6	0.23			
1800	35.6 / 10.9	0.16			
2500	42.4 / 12.9	0.13			
5800	66.8 / 20.4	0.09			