

### CONNECTOR LEGEND

ST Connector

SC Connector

FC Connector

Clipped LC Connector

MT-RJ Connector

**FODSTC-XX**  
• Dual ST Connectors

ST (2)

**FODSC-XX**  
• Dual SC Connectors

SC (2)

**FODFC-XX**  
• Dual FC Connectors

FC (2)

**FODLC-CL-XX**  
• Dual LC Clipped Connectors

LC (2)

**FODMTRJ-XX**  
• MT-RJ Connectors  
• Dual Fiber / Single Jacket

MT-RJ

**FODMTRJ-XX**  
• MT-RJ Connectors  
• One Connector has Pins

MT-RJ

**FODFC-LC-XX**  
• Dual FC and Dual LC Connectors

FC (2)

LC (2)

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

**62.5/125** L-com's multimode fiber optic patch cords and adapter cords utilize OFNR Riser Rated jackets. All cables are 100% optically tested and utilize a PC polish. Custom lengths and other connector types are available. All cable measurements are in meters. 1m = 3.28 ft.

**✓RoHS Dual ST to Dual ST Duplex Patch Cord, Multimode Fiber with OFNR Jacket**

<a href="#">FODSTC-01</a>	MM Fiber Cable, Dual ST / Dual ST, 1.0m	16.00	15.36	14.72	13.60	12.00
<a href="#">FODSTC-02</a>	MM Fiber Cable, Dual ST / Dual ST, 2.0m	17.25	16.56	15.87	14.66	12.94
<a href="#">FODSTC-03</a>	MM Fiber Cable, Dual ST / Dual ST, 3.0m	18.50	17.76	17.02	15.73	13.88
<a href="#">FODSTC-04</a>	MM Fiber Cable, Dual ST / Dual ST, 4.0m	19.75	18.96	18.17	16.79	14.81
<a href="#">FODSTC-05</a>	MM Fiber Cable, Dual ST / Dual ST, 5.0m	21.00	20.16	19.32	17.85	15.75
<a href="#">FODSTC-10</a>	MM Fiber Cable, Dual ST / Dual ST, 10.0m	27.25	26.16	25.07	23.16	20.44
<a href="#">FODSTC-15</a>	MM Fiber Cable, Dual ST / Dual ST, 15.0m	33.50	32.16	30.82	28.48	25.13
<a href="#">FODSTC-20</a>	MM Fiber Cable, Dual ST / Dual ST, 20.0m	39.75	38.16	36.57	33.79	29.81
<a href="#">FODSTC-25</a>	MM Fiber Cable, Dual ST / Dual ST, 25.0m	46.00	44.16	42.32	39.10	34.50
<a href="#">FODSTC-30</a>	MM Fiber Cable, Dual ST / Dual ST, 30.0m	52.25	50.16	48.07	44.41	39.19
<a href="#">FODSTC-35</a>	MM Fiber Cable, Dual ST / Dual ST, 35.0m	58.50	56.16	53.82	49.73	43.88
<a href="#">FODSTC-40</a>	MM Fiber Cable, Dual ST / Dual ST, 40.0m	64.75	62.16	59.57	55.04	48.56
<a href="#">FODSTC-45</a>	MM Fiber Cable, Dual ST / Dual ST, 45.0m	71.00	68.16	65.32	60.35	53.25

**✓RoHS Dual SC to Dual SC Duplex Patch Cord, Multimode Fiber with OFNR Jacket**

<a href="#">FODSC-01</a>	MM Fiber Cable, Dual SC / Dual SC, 1.0m	16.00	15.36	14.72	13.60	12.00
<a href="#">FODSC-02</a>	MM Fiber Cable, Dual SC / Dual SC, 2.0m	17.75	17.04	16.33	15.09	13.31
<a href="#">FODSC-03</a>	MM Fiber Cable, Dual SC / Dual SC, 3.0m	18.50	17.76	17.02	15.73	13.88
<a href="#">FODSC-04</a>	MM Fiber Cable, Dual SC / Dual SC, 4.0m	19.75	18.96	18.17	16.79	14.81
<a href="#">FODSC-05</a>	MM Fiber Cable, Dual SC / Dual SC, 5.0m	21.00	20.16	19.32	17.85	15.75
<a href="#">FODSC-10</a>	MM Fiber Cable, Dual SC / Dual SC, 10.0m	27.25	26.16	25.07	23.16	20.44
<a href="#">FODSC-15</a>	MM Fiber Cable, Dual SC / Dual SC, 15.0m	33.50	32.16	30.82	28.48	25.13
<a href="#">FODSC-20</a>	MM Fiber Cable, Dual SC / Dual SC, 20.0m	39.75	38.16	36.57	33.79	29.81
<a href="#">FODSC-25</a>	MM Fiber Cable, Dual SC / Dual SC, 25.0m	46.00	44.16	42.32	39.10	34.50
<a href="#">FODSC-30</a>	MM Fiber Cable, Dual SC / Dual SC, 30.0m	52.25	50.16	48.07	44.41	39.19
<a href="#">FODSC-35</a>	MM Fiber Cable, Dual SC / Dual SC, 35.0m	58.50	56.16	53.82	49.73	43.88
<a href="#">FODSC-40</a>	MM Fiber Cable, Dual SC / Dual SC, 40.0m	64.75	62.16	59.57	55.04	48.56
<a href="#">FODSC-45</a>	MM Fiber Cable, Dual SC / Dual SC, 45.0m	71.00	68.16	65.32	60.35	53.25

**✓RoHS Dual FC to Dual FC Duplex Patch Cord, Multimode Fiber with OFNR Jacket**

<a href="#">FODFC-01</a>	MM Fiber Cable, Dual FC / Dual FC, 1.0m	18.75	18.00	17.25	15.94	14.06
<a href="#">FODFC-02</a>	MM Fiber Cable, Dual FC / Dual FC, 2.0m	20.00	19.20	18.40	17.00	15.00
<a href="#">FODFC-03</a>	MM Fiber Cable, Dual FC / Dual FC, 3.0m	21.25	20.40	19.55	18.06	15.94
<a href="#">FODFC-04</a>	MM Fiber Cable, Dual FC / Dual FC, 4.0m	22.50	21.60	20.70	19.13	16.88
<a href="#">FODFC-05</a>	MM Fiber Cable, Dual FC / Dual FC, 5.0m	23.75	22.80	21.85	20.19	17.81

**✓RoHS Dual LC to Dual LC Clipped Duplex Patch Cord, Multimode Fiber with OFNR Jacket**

<a href="#">FODLC-CL-01</a>	MM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 1.0m	20.00	19.60	19.20	18.80	18.40
<a href="#">FODLC-CL-02</a>	MM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 2.0m	21.00	20.58	20.16	19.74	19.32
<a href="#">FODLC-CL-03</a>	MM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 3.0m	22.00	21.56	21.12	20.68	20.24
<a href="#">FODLC-CL-04</a>	MM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 4.0m	23.00	22.54	22.08	21.62	21.16
<a href="#">FODLC-CL-05</a>	MM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 5.0m	24.00	23.52	23.04	22.56	22.08
<a href="#">FODLC-CL-10</a>	MM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 10.0m	29.00	28.42	27.84	27.26	26.68

**✓RoHS MT-RJ to MT-RJ Duplex Patch Cord - Multimode Fiber with OFNR Jacket**

**Note:** These MT-RJ connectors do not utilize alignment pins.

<a href="#">FODMTRJ-01</a>	MM Fiber Cable, MT-RJ / MT-RJ, 1.0m	16.00	15.36	14.72	13.60	12.00
<a href="#">FODMTRJ-02</a>	MM Fiber Cable, MT-RJ / MT-RJ, 2.0m	17.25	16.56	15.87	14.66	12.94
<a href="#">FODMTRJ-03</a>	MM Fiber Cable, MT-RJ / MT-RJ, 3.0m	18.50	17.76	17.02	15.73	13.88
<a href="#">FODMTRJ-04</a>	MM Fiber Cable, MT-RJ / MT-RJ, 4.0m	19.75	18.96	18.17	16.79	14.81
<a href="#">FODMTRJ-05</a>	MM Fiber Cable, MT-RJ / MT-RJ, 5.0m	21.00	20.16	19.32	17.85	15.75

**✓RoHS MT-RJ to MT-RJ Duplex Patch Cord with Pins - Multimode Fiber with OFNR Jacket**

**Note:** One MT-RJ connector features alignment pins.

<a href="#">FODMTRJP-01</a>	MM Fiber Cable, MT-RJ / MT-RJ, 1.0m	19.00	18.24	17.48	16.15	14.25
<a href="#">FODMTRJP-02</a>	MM Fiber Cable, MT-RJ / MT-RJ, 2.0m	20.25	19.44	18.63	17.21	15.19
<a href="#">FODMTRJP-03</a>	MM Fiber Cable, MT-RJ / MT-RJ, 3.0m	21.50	20.64	19.78	18.27	16.13
<a href="#">FODMTRJP-04</a>	MM Fiber Cable, MT-RJ / MT-RJ, 4.0m	22.75	21.84	20.93	19.34	17.06
<a href="#">FODMTRJP-05</a>	MM Fiber Cable, MT-RJ / MT-RJ, 5.0m	24.00	23.04	22.08	20.40	18.00

**✓RoHS Dual FC to Dual LC Duplex Adapter Cord, Multimode Fiber with OFNR Jacket**

<a href="#">FODFC-LC-01</a>	MM Fiber Cable, Dual FC / Dual LC, 1.0m	27.50	26.40	25.30	23.38	20.63
<a href="#">FODFC-LC-02</a>	MM Fiber Cable, Dual FC / Dual LC, 2.0m	28.75	27.60	26.45	24.44	21.56
<a href="#">FODFC-LC-03</a>	MM Fiber Cable, Dual FC / Dual LC, 3.0m	30.00	28.80	27.60	25.50	22.50
<a href="#">FODFC-LC-04</a>	MM Fiber Cable, Dual FC / Dual LC, 4.0m	31.25	30.00	28.75	26.56	23.44
<a href="#">FODFC-LC-05</a>	MM Fiber Cable, Dual FC / Dual LC, 5.0m	32.50	31.20	29.90	27.63	24.38

**Tip** *What is the MT-RJ connector? How does it work?*

The MT-RJ is one of the newly emerging *Small Form Factor* connectors that are becoming commonplace in the networking industry. The MT-RJ utilizes two fibers and integrates them into a single design that looks similar to a Black RJ45 modular connector. Alignment is completed through the use of two pins that mate with the connector. Transceiver jacks found on NICs and equipment typically have the pins built into them. Users need to be careful that one connector has alignment pins when mating two MT-RJ cables through a coupler.

MT-RJ Coupler

Alignment Pins