

Item #	Description	List Price
✓RoHS Brady TLS2200™ Premium Thermal Transfer Label Printer		
TLS2200	200 system offers the lightweight of a hand-held printer (2.75lbs), while providing the superior capabilities of thermal transfer printing. The Brady printer features a two-line liquid crystal display and produces smear proof, ultra clear print quality and faster output than most other printers on the market. Useful for printing barcodes as well as text and numbers with crystal clear accuracy on labels up to 2 inches wide. This means you can now print labels for wire markers, patch panels, circuit boards, cable markers and more, faster and easier than ever before. Includes a 6-month manufacturer's warranty.	
TLS2200	Premium Brady Thermal Transfer Printer	849.00
TLS2200	Replacement Ribbon for TLS2200	23.95
TLS2200-BP	Replacement Battery	95.00

✓RoHS Brady IDXPRT Handheld Labeling System

The IDXPRT is the first handheld cartridge based labeling system that can print die-cut labels, self-laminating labels and sleeves as well as continuous tapes...You name it IDXPRT prints it! Choose from two keyboard layouts, then select from a wide range of label materials engineered just for your application. That includes wire and cable markers, panel, rack and frame ID, facilities labels and specialty labels for labs and workspaces. The IDXPRT can be used with self-lams, sleeves and 90+ label styles including continuous tapes. Additionally, the IDXPRT can print on materials up to 1.5" wide and prints characters up to 1.25". It also provides 82 symbols plus bar codes.

IDXPRT-ABC	Brady IDXPRT Handheld Labeling System (ABC Layout)	399.95
IDXPRT-KEY	Brady IDXPRT Handheld Labeling System (Keyboard Layout)	399.95

✓RoHS Brady IDPAL™ Thermal Printer

Brady IDPAL hand-held labeling tool offers electrical installers an unbeatable combination - superior labels designed for outstanding adherence to round and curved surfaces - at an affordable price. Weighing only 1.2 lbs. fully loaded (cartridge and batteries), it fits comfortably in the hand, features all the standard electrical symbols and is easy to use. The label cartridge is top-loaded. Built-in intelligence senses tape size and automatically formats the label. A choice of performance tested labeling materials, label widths and lengths and fonts ensures a good match with a variety of applications. It's the ideal tool for wire and cable marking, component marking and general identification. Includes a 6-month manufacturer's warranty.

IDPAL	Brady Thermal Printer	99.00
-------	-----------------------	-------

Item #	Description	Labels per Roll	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----------------	-----	-------	-------	---------	---------

Brady Roll, Cartridge and Wraparound Cable Labels

Brady cable labels are made from durable, high quality vinyl and can be used in any cable labeling application. Please refer to the label dimensions sizing chart located on the bottom right hand side of this page.

✓RoHS [TLS2200](#) Labels for TLS2200 are Available in a Variety of Sizes

PTL1942Z	Cable Labels, 1.0"L x 1.0"W x .375"H	250	29.95	29.35	28.75	28.15	27.55
PTL3142Z	Cable Labels, 1.0"L x 1.5"W x .50"H	250	39.95	39.15	38.35	37.55	36.75
PTL2142Z	Cable Labels, 1.0"L x 2.5"W x .75"H	100	24.95	24.45	23.95	23.45	22.95

Note: Many other label types available, call your L-com Sales Representative for free Brady Literature.

✓RoHS Brady IDXPRT Voice/Data Cable Markers

These labels are Ideal for marking data cabling. The B-427 vinyl self-laminating material offers superior abrasion resistance and resists dirt, oils, solvents and water. Each label features a clear, non-printed area, which wraps around and over laminates the printed text. The IDXPRT automatically "multiple repeats" your text in the white print area. These labels are UL Recognized and support a temperature range of -94°F to 158°F (-70°C to 70°C).

XSL-102-427	Vinyl Labels, 0.50"L x 1.25"W x 0.375"H	250	27.95	27.39	26.83	26.27	25.71
XSL-103-427	Vinyl Labels, 1.00"L x 1.25"W x 0.50"H	250	44.95	44.05	43.15	42.25	41.35
XSL-115-427	Vinyl Labels, 1.50"L x 1.25"W x 0.50"H	250	39.95	39.15	38.35	37.55	36.75
XSL-29-427	Vinyl Labels, 0.50"L x 1.25"W x 0.50"H	500	49.95	48.95	47.95	46.95	45.95
XSL-30-427	Vinyl Labels, 0.75"L x 1.25"W x 0.50"H	250	37.95	37.19	36.43	35.67	34.91

Note: Many other label types available, call your L-com Sales Representative for free Brady Literature.

✓RoHS Cable Labels for the IDPAL

PAL375439	Label Cartridge, 21"L x .375"W	N.A.	18.00	17.64	17.28	16.92	16.56
PAL500439	Label Cartridge, 21"L x .50"W	N.A.	18.00	17.64	17.28	16.92	16.56
PAL750439	Label Cartridge, 21"L x .75"W	N.A.	21.00	20.58	20.16	19.74	19.32

✓RoHS Cable Labels - Wraparound Style, 3 Sizes to Choose From

CL0515	Cable Labels, .50"L x 1.5"W x .50"H	30	5.95	5.83	5.71	5.59	5.47
CL1150	Cable Labels, 1.0"L x 1.5"W x .50"H	30	7.95	7.79	7.63	7.47	7.31
CL1375	Cable Labels, 1.0"L x 3.75"W x 1.0"H	30	5.95	5.83	5.71	5.59	5.47

Note: CL Series labels are not intended for use with Brady printers.



[TLS2200](#)
CLEARER AND FASTER



IDXPRT-ABC



IDXPRT-KEY




THERMAL TRANSFER TYPE

MORE ECONOMICAL


IDPAL



[XSL-102-427](#)
Replacement Ribbon for IDXPRT



[PAL750439](#)
Replacement Ribbon for IDPAL



Tip *What size cable label is appropriate for the cable that I am using?*

SS OSS SECTION	IF YOU HAVE:	THEN USE:
	8 conductor flat silver satin	PTL1942Z 7 or CL0515
	Duplex fiber cord (zipcord)	PTL1942Z 7 or CL0515
	RG59 coaxial cable	CL1150 127, CL0515 or CL1150
	Cat. 5/5E/6 4 pair twisted pair	CL1150 127, XSL Series, CL0515 or CL1150
	Category 3 25 pair	CL1375 127, CL0515 , CL1150 or CL1375

For more useful information go to....
www.L-com.com/Resources