



## UTP20028T

### Specifications:

- Conforms to IEEE 802.3 10Base-2/T standard
- Meets FCC part 15 subject J, Class A requirements
- Connectors Support:
  - One AUJ connector for connection to host
  - One RJ-45 jack for Ethernet
- Cable Length:
  - 50m for transceiver drop cable
  - 100m for twisted pair
- Transmission:
  - Base band
- Topology:
  - Star
- Access Method:
  - CSMA/CD
- Transmission Rate:
  - 10 Megabits per second
- Operating temp:
  - 0-55 degrees Celsius
- Humidity:
  - 10-90% non-condensing

Distributed by:

**L-com**® CONNECTIVITY  
PRODUCTS

45 Beechwood Drive  
North Andover, MA 01845  
www.L-com.com  
E-mail: sales@L-com.com  
Fax: 978-689-9484  
Toll Free: 800-343-1455

### Accessories:

Transceiver ETP-20028T  
User's Manual

### Box Dimensions:

6.94(L) x 3.44(W) x 1.25(H)

### Bar Code / Country: