


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	TAKEN FROM DRAWING 97-042805. RELEASED	10/14/09	DFP
B	ECN 5396: RE-MODELED AND RE-DIMENSIONED	3/23/11	D.FRISIELLO



NOTES:

1. MATERIAL: .06 THICK COLD ROLLED STEEL.
2. PANEL FINISH: FLAT BLACK POWDER COAT.
3. SILKSCREEN COLOR: WHITE.
4. PANEL ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.
5. JACKS HAVE PRESS-ON COVERS THAT PROPERLY PUNCH DOWN 24 OR 26 AWG CONDUCTORS. (USE SUITABLE ARBOR PRESS OR PARALLEL-ACTION PLIERS)

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY TJC	4/28/97		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY AEM	4/28/97	CATEGORY RACK PANELS	
	APPROVED BY AEM	4/28/97	PRODUCT DESCRIPTION 1.75"X19" PNL W/16 RJ12 IDC JACK	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. PR175-1606	REV. B
			SCALE: NONE	CAD FILE: PR175-1606.SLDRW
				SHEET 1 OF 1