


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	12/28/00	McCORMICK
B	REVISED TABLE ECN# 1128	06/11/02	MCCORMICK
.	.	.	.
.	.	.	.



PART NUMBER	LENGTH	
	METERS	FEET
SFOST-SC-01	1.0	3.3
SFOST-SC-02	2.0	6.6
SFOST-SC-03	3.0	9.8
SFOST-SC-04	4.0	13.1
SFOST-SC-05	5.0	16.4

- NOTES:  
 1. SINGLEMODE CONNECTOR ASSEMBLIES UTILIZE PC POLISH.  
 2. ALL CONNECTORS ACCOMPANIED WITH DUST CAP (NOT SHOWN).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:  
 .X ±.1  
 .XX ±.05  
 .XXX ±.005  
 CABLE LENGTH TOLERANCE  
 <300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY C.McCORMICK	12/28/00
CHECKED BY	
DFP APPROVED BY R.CARRICK	01/22/01
	01/22/01

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

**L-com**<sup>®</sup> 45 BEECHWOOD DRIVE  
 CONNECTIVITY PRODUCTS NORTH ANDOVER, MA  
 01845

PRODUCT DESCRIPTION  
**9/125 SINGLEMODE FIBER**

DRAWING TITLE  
**OUTLINE DRAWING**

SIZE	FSCM NO.	DWG. NO.	REV.
<b>A</b>	<b>43321</b>	SFOST-SC-01-OD1	<b>B</b>
SCALE 1:2	CAD FILE: SFOST-SC-01-OD1.SLDDRW	SHEET 1	OF 1