



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/20/14	D.GRIFFIN



MODEL NUMBER	LENGTH FEET [METERS]
TRD695PL-1	1.0 [.31]
TRD695PL-2	2.0 [.61]
TRD695PL-3	3.0 [.91]
TRD695PL-5	5.0 [1.52]
TRD695PL-7	7.0 [2.13]
TRD695PL-10	10.0 [3.05]
TRD695PL-15	15.0 [4.57]
TRD695PL-20	20.0 [6.10]
TRD695PL-25	25.0 [7.62]
TRD695PL-30	30.0 [9.14]
TRD695PL-40	40.0 [12.20]
TRD695PL-50	50.0 [15.24]
TRD695PL-60	60.0 [18.29]
TRD695PL-75	75.0 [22.86]
TRD695PL-100	100.0 [30.48]

NOTES:

MATERIAL:

PLUG HOUSING: POLYCARBONATE, CLEAR, UL94V-0
 CONTACTS: PHOSPHOR BRONZE
 CABLE JACKET: PLENUM, WHITE
 PLUG SHIELDING: BRASS

FINISH:

CONTACTS: 50 μINCHES GOLD IN CONTACT AREA
 OVER 100 μINCHES NICKEL PLATE OVERALL
 PLUG SHIELDING: NICKEL PLATED

CABLE CHARACTERISTICS:

UNSHIELDED, FOUR TWISTED PAIR, CAT 6 MODULAR CABLE
 CONDUCTORS: 23 AWG SOLID COPPER

MISCELLANEOUS:

PLUG CONFORMS TO TIA-1096
 OPERATING TEMPERATURE RANGE: 0°C TO +60°C
 CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.27]	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY D.GUITADAURO APPROVED BY M.MARTINEZ	DATE 10/10/14 10/16/14 10/16/14	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR		
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TRD695PL	REV. A
	SCALE: NONE		CAD FILE: TRD695PL.SLDDRW		SHEET 1 OF 1	