

















Cat. 6A/Class E_A Modular Plug AWG24-22/1, AWG26/7

<p>1 Scope of delivery</p>  <p>Gray AWG#22-23</p> <p>White AWG#24-26</p>	<p>2</p>  <p>min. 25mm</p> <p>Stripping length</p>  <p>Fold braid shield backwards</p>  <p>Wrap braid shield evenly around cable jacket</p>	<p>3</p> <p>T568B</p>  <p>Gray AWG#22-23</p> <p>White AWG#24-26</p>  <p>Untwist pairs and insert them into wire manager</p>	<p>4</p>  <p>Step 1</p>  <p>Step 2</p>
<p>5</p> <p>Cut wires</p>  <p>Step 1</p>  <p>Step 2</p>	<p>6</p> <p>T568B</p>  <p>Keep foil for better performance</p>	<p>7</p> 	<p>8</p> 
<p>9</p>  <p>Click</p>	<p>10</p>  <p>Place the metal cover onto the plug</p>	<p>11</p>  <p>Slide cable boot forward until snap-in (1)</p>  <p>1 ← 2</p> <p>Tighten cable gland until stop (2)</p>	<p>12</p> 