




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/10/2023	GUTTADAURO

WIRING MAP	
"J1"	"J2"
A2	A2
A3	A3
A4, B9	A4, B9
A9, B4	A9, B4
A5	A5
A6	A6
A7	A7
A8	A8
A10	A10
A11	A11
B2	B2
B3	B3
B5	B5
B6	B6
B7	B7
B8	B8
B10	B10
B11	B11
A1, A12	A1, A12
B1, B12	B1, B12
SHELL	SHELL




2X TYPE C FEMALE CONNECTOR

NOTES:

CONDUCTOR RESISTANCE: $\leq 10\Omega$
 INSULATION RESISTANCE: $\geq 5M\Omega$
 WITHSTAND VOLTAGE: DC 300V / 10ms

- ADAPTER SHALL BE TESTED FOR CONTINUITY.
- ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5] FRACTIONS $\pm 1/32$.XX = $\pm .02$ [.5] ANGLES $\pm 1^\circ$.XXX = $\pm .005$ [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DFRISIELLO	01/06/2023	
APPROVED BY GUTTADAURO	01/06/2023	CATEGORY USB 4.0	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION USB 4.0 Adapter, 40 GBPS, Straight Connector, F-F	
COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. CAU4C-ADP-FF
SCALE: NONE		CAD FILE: CAU4C-ADP-FF.SLDDRW	
			SHEET 1 OF 1