



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/10/2023	GUTTADAURO


"J1"
USB TYPE C FEMALE
CONNECTOR



WIRING MAP	
"J1"	"P1"
A1	A1
A2	A2
A3	A3
A4	A4
A5	A5
A6	A6
A7	A7
A8	A8
A9	A9
A10	A10
A11	AA11
A12	A12
B1	B1
B2	B2
B3	B3
B4	B4
B5	B5
B6	B6
B7	B7
B8	B8
B9	B9
B10	B10
B11	B11
B12	B12
SHELL	SHELL



"P1"
USB TYPE C MALE
CONNECTOR




NOTES:

CONDUCTOR RESISTANCE: $\leq 10\Omega$
 INSULATION RESISTANCE: $\geq 5M\Omega$
 WITHSTAND VOLTAGE: DC 300V / 10ms

- ADAPTER SHALL BE TESTED FOR CONTINUITY.
- ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5] FRACTIONS $\pm 1/32$.XX = $\pm .02$ [.5] ANGLES $\pm 1^\circ$.XXX = $\pm .005$ [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY DFRISIELLO	01/06/2023		CATEGORY USB 4.0	
	CHECKED BY RCARLES	01/06/2023			
	APPROVED BY GUTTADAURO	01/06/2023			
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION USB 4.0 Adapter, 40 GBPS, U/D Connector, M-F			
	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. CAU4C-UDADP-MF	REV. A
SCALE: NONE		CAD FILE: CAU4C-UDADP-MF.SLDDRW		SHEET 1 OF 1	