


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/29/2022	Guttadauro



P1
USB TYPE C
MALE CONNECTOR
NICKEL PLATED

P2
USB TYPE C
MALE CONNECTOR
NICKEL PLATED
WITH I.C. CHIP

4 PAIR 32AWG INDIVIDUALLY SHIELDED TINNED COPPER WITH ALUM/POLY FOIL SHIELD AND DRAIN WIRE
1 PAIR 32AWG STRANDED TINNED COPPER
4 CONDUCTOR 32AWG STRANDED TINNED COPPER
1 CONDUCTOR 23AWG STRANDED TINNED COPPER
OVERALL ALUM/POLY FOIL SHIELD, OVERALL BRAID SHIELD PLUS 2 TINNED COPPER DRAIN WIRES
JACKET: BLACK PVC WITH BLACK NYLON BRAID

WIRING MAP	
P1	P2
A2	B11
A3	B10
B11	A2
B10	A3
A10	B3
A11	B2
B3	A10
B2	A11
A5	A5
B5	B5
B8	A8
A8	B8
A6	A6
A7	A7
A1, B1, A12, B12 SHELL	A1, B1, A12, B12 SHELL
A4, B4, A9, B9	A4, B4, A9, B9

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. PASS 100W (20V5A) 40G 4K@60Hz 5K@60Hz 8K@60Hz TEST.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [5] ANGLES ± 1° .XXX = ±.005 [1.3]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DFRISIELLO CHECKED BY RCARLESCO APPROVED BY Guttadauro	11/29/2022 11/29/2022 11/29/2022	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION USBC 4.0-40G/100W, M-M, Metal Plug	
	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321 ITEM NO. CAU4CC-40M-05M SCALE: NONE CAD FILE: CAU4CC-40M-05M.SLDDRW SHEET 1 OF 1