


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	07/06/2023	SREITER	GUTTADAURO




PIN 1	RED	PIN 1
PIN14	GND1	PIN14
PIN 2	BLACK	PIN25
PIN15	PINK	PIN12
PIN 3	PINK	PIN24
PIN16	WHITE	PIN11
PIN 4	BLUE	PIN23
PIN17	BLACK	PIN10
PIN 5	WHITE	PIN22
PIN18	BROWN	PIN 9
PIN 6	BLACK	PIN21
PIN19	ORANGE	PIN 8
PIN 7	GREEN	PIN20
PIN20	WHITE	PIN 7
PIN 8	GREEN	PIN19
PIN21	BLACK	PIN 6
PIN 9	WHITE	PIN18
PIN22	ORANGE	PIN 5
PIN10	BLACK	PIN17
PIN23	BROWN	PIN 4
PIN11	BLUE	PIN16
PIN24	WHITE	PIN 3
PIN12	WHITE	PIN15
PIN25	BLACK	PIN 2
PIN13	GND(2)	PIN13
PIN26	BLACK	PIN26
SHELL	BRAID	SHELL

PART NO.	LENGTH	
	FEET	METERS
CLCA06-3M	9.8	3
CLCA06-5M	16.4	5

- NOTES:
1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENTLY RELEASED VERSION).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		L-com[™] an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936				
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]		DRAWN BY SREITER		07/06/2023						
		CHECKED BY DGUST		07/06/2023						
		APPROVED BY GUTTADAURO		07/06/2023						
THIRD-ANGLE PROJECTION 		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY CAMERA LINK ASSEMBLY						
				PRODUCT DESCRIPTION CAMERA LINK MACHINE VISION CABLE ASSEMBLY, SDR26 MALE PLUG TO SDR26 MALE PLUG, BLACK 29AWG CABLE						
				SIZE A		CAGE CODE 43321		ITEM NO. CLCA06		REV. A
				SCALE: NONE		CAD FILE: CLCA06-5M.SLDDRW		SHEET 1 OF 1		