

6

5


4

3

2

1

REVISION				
ZONE	REV	DESCRIPTION	DATE	CHANGED BY
	B	UPDATED PER ECO-13914	10/07/2024	HBAKKE
				GUTTADAURO



NOTES:

- VOLTAGE TEST: DC 300V 10MS
INSULATION RESISTANCE: 5.0M ohm/min.
CONDUCTANCE RESISTANCE: 5.0 ohm/max.
- 2X #4-40 UNC-2A X .38" LG SCREW INCLUDED. (NOT SHOWN)
- DUST CAPS INSTALLED AT SHIPPING. (NOT SHOWN)
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

6

5

4

3

2

1

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		L-com® an INFINIT@ brand Website: www.L-com.com Phone: 1.800.341.5266 1.978.682.6936		 	
TOLERANCES:				INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
X = ± .2 [5] .XX = ± .02 [0.5] .XXX = ± .005 [0.13]		FRACTIONS ± 1/32 ANGLES ± 1°		SCALE NONE	SHEET 1 OF 1
CABLE LENGTH TOLERANCES: ≤12 [305] = ±1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DESCRIPTION DISPLAYPORT 2.0 CABLE ASSEMBLY, M/F-PM, LSZH, BLK			
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UN-DIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY		SIZE A	CAGE CODE 43321	DRAWN BY DFRISIELLO	ITEM NO. DP20Z-MFP-BLK
					REV B