







THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION		DESCRIPTION	DATE	CHANGED BY	APPROVED
ZONE	REV	INITIAL RELEASE	03/06/2023	HBAKKE	PHOSPODAR



RECOMMENDED  
PANEL CUTOUT

NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DUST CAPS NOT SHOWN.
3. RECOMMENDED PANEL THICKNESS: .05-.07" [1.2-1.7mm]
4. STANDARDS: IEC 61754-20, TIA/EIA 604-10A-2002, TELCORDIA GR-326-CORE
5. INSERTION LOSS: <0.2dB
6. OPERATING/STORAGE TEMPERATURE: -40 TO +85°C
7. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:  
 $\leq 12$  [305] = +1 [25] / -0  
 $> 12$  [305]  $\leq 60$  [1524] = +2 [51] / -0  
 $> 60$  [1524]  $\leq 120$  [3048] = +4 [102] / -0  
 $> 120$  [3048]  $\leq 300$  [7620] = +6 [152] / -0  
 $> 300$  [7620] = +5% / -0

ALL OTHER DIMENSIONAL TOLERANCES:  
 $.X = \pm .2$  [5] FRACTIONS  
 $.XX = \pm .02$  [5]  $\pm 1/32$   
 $.XXX = \pm .005$  [1.3] ANGLES  $\pm 1^\circ$

CONFIGURATION DETAILS OF  
UNDIMENSIONED FEATURES  
MAY VARY

THIRD-ANGLE PROJECTION

COLOR VARIATIONS  
MAY OCCUR

APPROVALS

DATE

DRAWN BY

03/06/2023

CHECKED BY

03/06/2023

APPROVED BY

03/06/2023

REV.

**L-COM**  
an INFINIT<sup>®</sup> brand

50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936

FIBER OPTICS

CATEGORY

PRODUCT DESCRIPTION

Fiber Coupler, LC/LC SlimLine Quad, White Internal Shutter, Vertical Spring, High Density Reduced Height, No Flange, Blue

SIZE

A

CAGE CODE

43321

ITEM NO.

FOA-837-BLU

REV.

A

SCALE:

NONE

CAD FILE: foa-837-blu.SLDDRW

SHEET 1 OF 1