







THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION				
ZONE	REV	DESCRIPTION	DATE	CHANGED BY
	A	INITIAL RELEASE	08/15/2023	DZINN PHOSODAR



MTG HOLE  
1.7mm MAX THK  
REF ONLY



#### NOTES:

1. ADAPTER SUPPLIED WITH 4 DUST CAPS INSTALLED WHICH ARE NOT SHOWN.
2. ADAPTER SHALL BE INDIVIDUALLY PACKAGED IAW L-COM SPECIFICATION PS-0031.

#### REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:  
 $\leq 12$  [305] =  $+1$  [25] / -0  
 $> 12$  [305]  $\leq 60$  [1524] =  $+2$  [51] / -0  
 $> 60$  [1524]  $\leq 120$  [3048] =  $+4$  [102] / -0  
 $> 120$  [3048]  $\leq 300$  [7620] =  $+6$  [152] / -0  
 $> 300$  [7620] =  $+5\%$  / -0

ALL OTHER DIMENSIONAL TOLERANCES:

$.X = \pm .2$  [5]      FRACTIONS  
 $.XX = \pm .02$  [5]       $\pm 1/32$   
 $.XXX = \pm .005$  [1.3]      ANGLES  $\pm 1^\circ$



APPROVALS

DRAWN BY  
DZINN

08/15/2023

CHECKED BY  
KGLEBOVA

08/15/2023

APPROVED BY  
JJOHNSTON

08/15/2023

DATE

**L-COM**  
an INFINIT<sup>®</sup> brand

50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936

CATEGORY

FIBER OPTIC

CONFIGURATION DETAILS OF  
UNDIMENSIONED FEATURES  
MAY VARY

PRODUCT DESCRIPTION  
CS DUAL CHANNEL (4F) ADAPTER,  
NO FLANGE, AQUA

SIZE

A

CAGE CODE

43321

ITEM NO.

FOA-CS2-05

REV.

A

SCALE: NONE

CAD FILE: FOA-CS2-05.SLDDRW

SHEET 1 OF 1