



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISION				
ZONE	REV	DESCRIPTION	DATE	CHANGED BY
	A	INITIAL RELEASE	08/15/2023	DZINN
				PHOSPODAR





$.37^{+.02}_{-.00}$
 $9.4^{+.05}_{0.0}$
 $2X \phi .094^{+.008}_{-.000} [2.4^{+.02}_{0.0}]$



MTG HOLE
1.7mm MAX THK
REF ONLY



.183
[4.65]



NOTES:

- ADAPTER SUPPLIED WITH 8 DUST CAPS INSTALLED WHICH ARE NOT SHOWN.
- ADAPTER SHALL BE INDIVIDUALLY PACKAGED IAW L-COM SPECIFICATION PS-0031.


REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:
≤12 [305] = +1 [25] / -0
>12 [305] ≤60 [1524] = +2 [51] / -0
>60 [1524] ≤120 [3048] = +4 [102] / -0
>120 [3048] ≤300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL OTHER DIMENSIONAL TOLERANCES:
.X = ±.2 [5] | FRACTIONS
.XX = ±.02 [5] | ± 1/32
.XXX = ±.005 [13] | ANGLES ± 1°

THIRD-ANGLE PROJECTION



APPROVALS	DATE
DRAWN BY DZINN	08/15/2023
CHECKED BY KGLEBOVA	08/15/2023
APPROVED BY JJOHNSTON	08/15/2023

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

COLOR VARIATIONS
MAY OCCUR

L-com
an INFINITI® brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

FIBER OPTIC

PRODUCT DESCRIPTION

CS QUAD CHANNEL (8F) ADAPTER,
WITH FLANGE, BLUE

SIZE
A

CAGE CODE
43321

ITEM NO.

FOA-CS4-11

REV.
A

SCALE: NONE

CAD FILE: FOA-CS4-11.SLDDRW

SHEET 1 OF 1