




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/28/2023	KGLEBOVA	GUTTADAURO



EXPLODED VIEW

PART TABLE	
ITEM	DESCRIPTION
1	COVER CASE
2	GUIDE
3	SHIELD SHELL
4	PLUG UNIT
5	SHIELD CASE
6	COVER CASE


NOTES:

MECHANICAL DATA:

- CONDUCTOR SIZE: 24AWG - 26AWG.
7 STRANDED, ANNEALED COPPER WIRE.
- INSULATION O.D.: 1.1mm TO 1.25mm.
- BRAID SHIELD: TIN PLATING.
- CABLE O.D.: Ø6.3mm TO Ø7.2mm.

MISCELLANEOUS:

- THIS DRAWING SHOWS IX31G-B-10S-CVL2(7.0).
- THIS PRODUCT (TYPE B) IS USED FOR NON ETHERNET APPLICATIONS LIKE SIGNALING, SERIAL OR OTHER INDUSTRIAL BUS COMMUNICATION SYSTEMS. PLEASE USE TYPE A FOR 10/100 MBIT/S AND 1/10 GBIT/S ETHERNET COMMUNICATION.
- PRODUCT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- SHIPS UNASSEMBLED AND SHIELD SHELL IS PRE-BENT.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		L-com™ an INFINIT® brand		50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936			
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [5] ANGLES ± 1° .XXX = ±.005 [13]		DRAWN BY KGLEBOVA		04/12/2023		CATEGORY TELECOM / MODULAR					
		CHECKED BY BPUCHASKI		04/17/2023							
		APPROVED BY GUTTADAURO		04/20/2023							
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION IX INDUSTRIAL RIGHT ANGLE PLUG, 10gig, B KEY, 90° UP DESIGN, IDC CRIMP TYPE 24-26AWG RANGE									
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321		ITEM NO. IXP-C2426RAU-B		REV. A	
				SCALE: NONE		CAD FILE: IXP-C2426RAU-B.SLDDRW				SHEET 1 OF 1	