




8 7 6 5 4 3 2 1
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	ECO-12741	02/14/2022	DZINN	WDIBELLA



NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. ZINC PLATING THICKNESS $\geq 6 \mu\text{m}$.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	L-com TM an INFINIT [®] brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = $+1$ [25] / -0 > 12 [305] ≤ 60 [1524] = $+2$ [51] / -0 > 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0 > 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0 > 300 [7620] = $+5\%$ / -0	DRAWN BY DZINN	02/14/2022	CATEGORY				
	CHECKED BY VCHAN	02/28/2022			RACK ACCESSORIES		
	APPROVED BY WDIBELLA	02/28/2022			PRODUCT DESCRIPTION		
ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2$ [5] $.XX = \pm .02$ [5] $.XXX = \pm .005$ [1.3]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY						
FRACTIONS $\pm 1/32$ ANGLES $\pm 1^\circ$	THIRD-ANGLE PROJECTION						
	COLOR VARIATIONS MAY OCCUR						
	SIZE A	CAGE CODE 43321	ITEM NO. LC-HHK	REV. B			
	SCALE: NONE	CAD FILE: LC-HHK.SLDDRW			SHEET 1 OF 1		