




6 5 4 3 2 1



REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	12/07/2023	KGLEBOVA	THOUGHTON




SECTION C-C



SECTION D-D



SECTION A -A

DETAIL B
2 PLACES

NOTES:

1. PACKAGING: SHALL BE PACKAGED AS PER L-COM SPEC PKG-00070
2. ALL DIMENSIONS FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENTLY RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
 $X = \pm .2$ [5] FRACTIONS
 $XX = \pm .02$ [0.5] $\pm 1/32$
 $XXX = \pm .005$ [0.13] ANGLES $\pm 1^\circ$

CABLE LENGTH TOLERANCES:
 ≤ 12 [305] ± 1 [25] / -0
 > 12 [305] ≤ 60 [1524] ± 2 [51] / -0
 > 60 [1524] ≤ 120 [3048] ± 4 [102] / -0
 > 120 [3048] ≤ 300 [7620] ± 6 [152] / -0
 > 300 [7620] $= \pm 5\%$ / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINITE brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5
SCALE NONE SHEET 1 OF 1

DESCRIPTION
PUSHBUTTON ENCLOSURE, 2 HOLE, 30.5MM, POLYESTER,
GRAY

SIZE A	CAGE CODE 43321	DRAWN BY KGLEBOVA	ITEM NO. LC-PCG-0813-1-A2	REV A
--------	-----------------	-------------------	---------------------------	-------