


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	05/08/2023	BPUCHASKI	AGANWANI



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:  
 $\leq 12$  [305] =  $+1$  [25] / -0  
 $> 12$  [305]  $\leq 60$  [1524] =  $+2$  [51] / -0  
 $> 60$  [1524]  $\leq 120$  [3048] =  $+4$  [102] / -0  
 $> 120$  [3048]  $\leq 300$  [7620] =  $+6$  [152] / -0  
 $> 300$  [7620] =  $+5\%$  / -0

ALL OTHER DIMENSIONAL TOLERANCES:  
 $.X = \pm .2$  [5]  
 $.XX = \pm .02$  [.5]  
 $.XXX = \pm .005$  [.13]



APPROVALS	DATE
DRAWN BY BPUCHASKI	05/08/2023
CHECKED BY KLEITLEIN	05/08/2023
APPROVED BY AGANWANI	05/08/2023

CONFIGURATION DETAILS OF  
UNDIMENSIONED FEATURES  
MAY VARY

COLOR VARIATIONS  
MAY OCCUR

**L-COM**<sup>TM</sup>  
an INFINIT<sup>®</sup> brand

50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936

CATEGORY

COAXIAL

PRODUCT DESCRIPTION  
BNC Male to BNC Female Cable  
Using RG316 Coax

SIZE	CAGE CODE	ITEM NO.	REV.
A	43321	LCCA31345	A
SCALE: NONE	CAD FILE: LCCA31345.SLDDRW		SHEET 1 OF 1