


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION

| ZONE | REV. | DESCRIPTION | DATE | CHANGED BY | APPROVED BY |
|------|------|-----------------|------------|------------|-------------|
| | A | INITIAL RELEASE | 05/08/2023 | BPUCHASKI | AGANWANI |



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

| | | | |
|---|--|--|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] | APPROVALS | DATE |  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 |
| OVERALL CABLE LENGTH TOLERANCE: | | | |
| ≤ 12 [305] = +1 [25] / -0 | DRAWN BY BPUCHASKI | 05/08/2023 | |
| > 12 [305] ≤ 60 [1524] = +2 [51] / -0 | CHECKED BY KLEITLEIN | 05/08/2023 | |
| > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 | APPROVED BY AGANWANI | 05/08/2023 | CATEGORY |
| > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 | | | COAXIAL |
| > 300 [7620] = +5% / -0 | | | |
| ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2$ [5] $.XX = \pm .02$ [.5] $.XXX = \pm .005$ [.13] | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | PRODUCT DESCRIPTION | |
| | | BNC Male Right Angle to SMA Female Cable Using RG316 Coax | |
| THIRD-ANGLE PROJECTION | COLOR VARIATIONS MAY OCCUR | SIZE A | CAGE CODE 43321 |
| | | ITEM NO. LCCA31352 | REV. A |
| | SCALE: NONE | CAD FILE: LCCA31352.SLDDRW | SHEET 1 OF 1 |