


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	3/21/2023	DMAY	DGUTTADAURO



P1
HDMI AM 19P
SHELL/PIN: GOLD PLATED
& TINPLATE

PIN Assignment	
P1 HDMI AM	P2 HDMI AM
1	1
3	3
2	2
4	4
6	6
5	5
7	7
9	9
8	8
10	10
12	12
11	11
14	14
19	19
17	17
13	13
15	15
16	16
18	18
SHELL	SHELL


P2
HDMI AM 19P
SHELL/PIN: GOLD PLATED
& TINPLATE

PART NUMBER	LENGTH	
	FEET	METERS
LHDMI21-BAMM-05M	1.64	0.5±.03
LHDMI21-BAMM-1M	3.28	1.0±.03

NOTES:

- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL, APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- DIMENSIONS FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [.13]	APPROVALS	DATE	L-com™ an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY DMAY	3/21/2023				
	CHECKED BY HBAKKE	3/21/2023	CATEGORY			
	APPROVED BY DGUTTADAURO	3/21/2023	AUDIO/VIDEO			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION HDMI 2.1 HDMI CABLE, M/M, BLUE ALUMINUM SHELL BLACK NYLON BRAID CABLE, 8K@60Hz, 4K@120Hz				
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. LHDMI21-BAMM	REV. A
			SCALE: NONE		CAD FILE: LHDMI21-BAMM.SLDDRW	SHEET 1 OF 1