

REVISION

| ZONE | REV | DESCRIPTION | DATE | CHANGED BY | APPROVED |
|------|-----|-------------|------------|------------|----------|
| | A1 | ECO-14004 | 11/15/2024 | KGLEBOVA | DGUST |

F

F

E

E

D

D

C




C

B

B

A

A

WIRING SPEC

| FROM RJ48C JACK | TO RJ48C JACK |
|--------------------|------------------|
| 1 | 3 |
| 2 | 6 |
| FROM RJ45 PLUG | TO RJ45 PLUG |
| 1 | 3 |
| 2 | 6 |

NOTES:

- TEST: 100% ELECTRICAL TEST AT 1M OHM
INSULATION RESISTANCE.
- CHAIN INCLUDED.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
 $X = \pm .2$ [5]
 $XX = \pm .02$ [0.5]
 $XXX = \pm .005$ [0.13]

| |
|----------------------|
| FRACTIONS |
| $\pm 1/32$ |
| ANGLES $\pm 1^\circ$ |

CABLE LENGTH TOLERANCES:
 ≤ 12 [305] = ± 1 [25] / -0
 > 12 [305] ≤ 60 [1524] = ± 2 [51] / -0
 > 60 [1524] ≤ 120 [3048] = ± 4 [102] / -0
 > 120 [3048] ≤ 300 [7620] = ± 6 [152] / -0
 > 300 [7620] = $\pm 5\%$ / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINITE[®] brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5
SCALE SHEET
NONE 1 OF 1

DESCRIPTION
CAT5e ETHERNET LOOPBACK ADAPTER RJ48C JACK & RJ45
PLUG, DARK BLUE

| | | | | |
|------|-----------|----------|--------------|-----|
| SIZE | CAGE CODE | DRAWN BY | ITEM NO. | REV |
| A | 43321 | DMAY | LLBADPC5E-BL | A1 |