


## REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	ECO-14321	3/13/2025	TDUFRENE	REVANGELIS



WIRING MAP  
TYPE B

J1	COLOR	J2
1	BLUE	12
2	ORANGE	11
3	GREEN	10
4	BROWN	9
5	GRAY	8
6	WHITE	7
7	RED	6
8	BLACK	5
9	YELLOW	4
10	PURPLE	3
11	ROSE	2
12	AQUA	1

LENGTH	
ITEM NO.	METERS [FEET]
MPFF12OM3BR-1	1.0 [3.28]
MPFF12OM3BR-3	3.0 [9.84]
MPFF12OM3BR-5	5.0 [16.40]
MPFF12OM3BR-10	10.0 [32.81]

REGULATORY COMPLIANCE:  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:  
 $X = \pm .2$  [5]      FRACTIONS  
 $XX = \pm .02$  [0.5]       $\pm 1/32$   
 $XXX = \pm .005$  [0.13]      ANGLES  $\pm 1^\circ$

CABLE LENGTH TOLERANCES:  
 $\leq 12$  [305] =  $\pm 1$  [25] / -0  
 $> 12$  [305]  $\leq 60$  [1524] =  $\pm 2$  [51] / -0  
 $> 60$  [1524]  $\leq 120$  [3048] =  $\pm 4$  [102] / -0  
 $> 120$  [3048]  $\leq 300$  [7620] =  $\pm 6$  [152] / -0  
 $> 300$  [7620] =  $\pm 5\%$  / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINITE brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5  
SCALE      SHEET  
NONE      1 OF 1

DESCRIPTION  
FIBER PATCH CABLE MPO FEMALE TO MPO FEMALE, 12 FIBER  
MMF OM3 TYPE B, OFNR RATED

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DZINN	MPFF12OM3BR	B