


8 7 6 5 4 3 2 1  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/22/21	PHOSPODAR

WIRING MAP TYPE A		
J1	COLOR	J2
1	BLUE	1
2	ORANGE	2
3	GREEN	3
4	BROWN	4
5		5
6		6
7		7
8		8
9	YELLOW	9
10	PURPLE	10
11	ROSE	11
12	AQUA	12



LENGTH	
ITEM NO.	METERS [FEET]
MPFF8OM3AP-1	1.0 [3.28]
MPFF8OM3AP-3	3.0 [9.84]
MPFF8OM3AP-5	5.0 [16.40]
MPFF8OM3AP-10	10.0 [32.81]

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES [mm]  
OVERALL CABLE LENGTH TOLERANCE:  
≤12 [305] = +1 [25] / -0  
>12 [305] ≤60 [1524] = +2 [51] / -0  
>60 [1524] ≤120 [3048] = +4 [102] / -0  
>120 [3048] ≤300 [7620] = +6 [152] / -0  
>300 [7620] = +5% / -0

ALL OTHER DIMENSIONAL TOLERANCES:  
.X = ± .2 [5] FRACTIONS  
.XX = ± .02 [5] ± 1/32  
.XXX = ± .005 [.13] ANGLES ± 1°



APPROVALS  
DRAWN BY  
DZINN  
10/22/2021  
CHECKED BY  
DFRISIELLO  
10/22/2021  
APPROVED BY  
PHOSPODAR  
10/22/2021

CONFIGURATION DETAILS OF  
UNDIMENSIONED FEATURES  
MAY VARY

COLOR VARIATIONS  
MAY OCCUR

DATE  
10/22/2021  
CATEGORY  
FIBER OPTICS

PRODUCT DESCRIPTION  
Fiber patch cable MPO female to MPO female, 8 fiber MMF OM3 type A, OFNP rated

SIZE  
**A**  
CAGE CODE  
**43321**  
ITEM NO.  
**MPFF8OM3AP**  
REV.  
**A**

SCALE: NONE CAD FILE: MPFF8OM3AP.SLDDRW SHEET 1 OF 1

50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936