


8 7 6 5 4 3 2 1  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/22/2021	PHOSPODAR

WIRING MAP TYPE B		
J1	COLOR	J2
1	BLUE	12
2	ORANGE	11
3	GREEN	10
4	BROWN	9
5	GRAY	8
6	WHITE	7
7	RED	6
8	BLACK	5
9	YELLOW	4
10	PURPLE	3
11	ROSE	2
12	AQUA	1



LENGTH	
ITEM NO.	METERS [FEET]
MPMM12SMBP-1	1.0 [3.28]
MPMM12SMBP-3	3.0 [9.84]
MPMM12SMBP-5	5.0 [16.40]
MPMM12SMBP-10	10.0 [32.81]

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE:  <math>\leq 12</math> [305] = +1 [25] / -0  <math>&gt; 12</math> [305] <math>\leq 60</math> [1524] = +2 [51] / -0  <math>&gt; 60</math> [1524] <math>\leq 120</math> [3048] = +4 [102] / -0  <math>&gt; 120</math> [3048] <math>\leq 300</math> [7620] = +6 [152] / -0  <math>&gt; 300</math> [7620] = +5% / -0         </p> <p>ALL OTHER DIMENSIONAL TOLERANCES:  <math>.X = \pm .2</math> [5]      FRACTIONS  <math>.XX = \pm .02</math> [5]      <math>\pm 1/32</math>  <math>.XXX = \pm .005</math> [1.3]      ANGLES <math>\pm 1^\circ</math> </p> <p>THIRD-ANGLE PROJECTION</p>	APPROVALS	DATE	 <p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p> <p>CATEGORY</p> <p>FIBER OPTICS</p>
	DRAWN BY DZINN	10/22/2021	
	CHECKED BY DFRISIELLO	10/22/2021	
<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p> <p>COLOR VARIATIONS MAY OCCUR</p>	APPROVED BY PHOSPODAR	10/22/2021	<p>PRODUCT DESCRIPTION</p> <p>Fiber patch cable MPO male to MPO male, 12 fiber SMF type B, OFNP rated</p> <p>SIZE <b>A</b>      CAGE CODE <b>43321</b>      ITEM NO. <b>MPMM12SMBP</b>      REV. <b>A</b></p> <p>SCALE: NONE      CAD FILE: MPMM12SMBP.SLDDRW      SHEET 1 OF 1</p>