

6

5

4

3


2

1

WIRING MAP  
TYPE B

MPO FIBER	COLOR	J1	J2
1	BLUE	1	24
2	ORANGE	2	23
3	GREEN	3	22
4	BROWN	4	21
5	GRAY	5	20
6	WHITE	6	19
7	RED	7	18
8	BLACK	8	17
9	YELLOW	9	16
10	VIOLET	10	15
11	ROSE	11	14
12	AQUA	12	13
13	BLUE	13	12
14	ORANGE	14	11
15	GREEN	15	10
16	BROWN	16	9
17	GRAY	17	8
18	WHITE	18	7
19	RED	19	6
20	BLACK	20	5
21	YELLOW	21	4
22	VIOLET	22	3
23	ROSE	23	2
24	AQUA	24	1
13 - 24 FIBER WITH BLACK BAR			

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	C	ECO-15269	6/10/2026	AKRESOWSKI	REVANGELIS



NOTES:

1. ALL CONNECTORS SUPPLIED WITH A DUST CAP INSTALLED (NOT SHOWN).
2. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IAW L-COM SPECIFICATION PS-0031.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS


TOLERANCES:  
 X = ±.2 [5]      FRACTIONS ± 1/32  
 .XX = ±.02 [0.5]      ANGLES ± 1°  
 .XXX = ±.005 [0.13]

CABLE LENGTH TOLERANCES:  
 ≤12 [305] = +1 [25] / -0  
 >12 [305] ≤ 60 [1524] = +2 [51] / -0  
 >60 [1524] ≤ 120 [3048] = +4 [102] / -0  
 >120 [3048] ≤ 300 [7620] = +6 [152] / -0  
 >300 [7620] = +5% / -0  
 CABLE LENGTH TOL IAW IPC A-620

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**<sup>®</sup>  
an INFINITE company

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE NONE	SHEET 1 OF 1
---------------	-----------------

DESCRIPTION  
MPO W/ PINS TO MPO W/ PINS, 24 FIBER, TYPE B, 40GB 50/125  
OM4 MMF, OFNR JACKET

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DMAY	MPMM24OM4BR	C

6

5

4

3

2

1