


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

8 7 6 5 4 3 2 1

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/16/2020	MBLACKWOOD

D

D



C

C

B

B

A

A

NOTE:

1. FOR INDOOR USE ONLY

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:
 ≤ 12 [305] = $+1$ [25] / -0
 > 12 [305] ≤ 60 [1524] = $+2$ [51] / -0
 > 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0
 > 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0
 > 300 [7620] = $+5\%$ / -0

ALL OTHER DIMENSIONAL TOLERANCES:
 $.X = \pm .2$ [5] FRACTIONS
 $.XX = \pm .02$ [.5] $\pm 1/32$
 $.XXX = \pm .005$ [.13] ANGLES $\pm 1^\circ$

THIRD-ANGLE PROJECTION

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

COLOR VARIATIONS
MAY OCCUR

APPROVALS

DATE

DRAWN BY

BPUCHASKI

12/16/2020

CHECKED BY

DFRISIELLO

12/16/2020

APPROVED BY

MBLACKWOOD

12/16/2020

L-COM
an INFINITe brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

POWER PRODUCTS

PRODUCT DESCRIPTION
**HOSPITAL GRADE NEMA 5-15P TO N6-15R
13 AMP - 1OFT**

SIZE **A** CAGE CODE **43321** ITEM NO. **PPA00036-10F** REV. **A**

SCALE: NONE CAD FILE: PPA00036-10F.SLDDRW

SHEET 1 OF 1