


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/11/2023	SREITER	GUTTADAURO



WIRING DIAGRAM

MALE CONNECTOR 1


1	BROWN	1
2	BLACK	2
3	WHITE	3
4	BLUE	4

MALE CONNECTOR 2

PART NUMBER	LENGTH	
	FEET	METERS
TR8401-C4B-1M	3.3	1
TR8401-C4B-3M	9.8	3
TR8401-C4B-5M	16.4	5

NOTES:

- 100% OPEN, SHORT, MISWIRE TEST
- INSULATION RESISTANCE: 10MΩ MIN, 300VDC;
CONDUCTOR RESISTANCE: 3Ω MAX
- WATERPROOF IP67
- LEAD-FREE SOLDER TIN
- OPERATING TEMPERATURE RANGE: -20°C~80°C
- CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED
IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1° THIRD-ANGLE PROJECTION 	APPROVALS	DATE			50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY SREITER	04/11/2023					CATEGORY
	CHECKED BY DGUST	04/11/2023					
	APPROVED BY GUTTADAURO	04/11/2023					
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CABLE ASSEMBLY				
PRODUCT DESCRIPTION M8 4 POSITION CABLE, PVC JACKET, MALE/MALE - 5M							
COLOR VARIATIONS MAY OCCUR			SIZE A	CAGE CODE 43321	ITEM NO. TR8401-C4B-5M	REV. A	
			SCALE: NONE		CAD FILE: TR8401-C4B-5M.SLDDRW	SHEET 1 OF 1	