


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/11/2023	SREITER	GUTTADAURO



WIRING DIAGRAM	
FEMALE CONNECTOR	OPEN
1	BROWN
2	BLACK
3	WHITE
4	BLUE

PART NUMBER	LENGTH	
	FEET	METERS
TR8403-C4B-1M	3.3	1
TR8403-C4B-3M	9.8	3
TR8403-C4B-5M	16.4	5

NOTES:

- 100% OPEN, SHORT, MISWIRE TEST
- INSULATION RESISTANCE: 10MΩ MIN, 300VDC;
CONDUCTOR RESISTANCE: 3Ω MAX
- WATERPROOF IP67
- LEAD-FREE SOLDER TIN
- OPERATING TEMPERATURE RANGE: -20°C~80°C
- CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED
IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS	DATE	L-COM an INFINITI brand	CATEGORY	PRODUCT DESCRIPTION
OVERALL CABLE LENGTH TOLERANCE:	≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY SREITER	04/11/2023			
ALL OTHER DIMENSIONAL TOLERANCES:	.X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13]	CHECKED BY DGUST	04/11/2023			
FRACTIONS ± 1/32 ANGLES ± 1°	APPROVED BY GUTTADAURO	04/11/2023				
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. TR8403-C4B-3M	REV. A
		SCALE: NONE	CAD FILE: TR8403-C4B-3M.SLDDRW			SHEET 1 OF 1