

6

5

4

3

2



1

PIN ASSIGNMENT


IX PIN #	COLOR	RJ45 PIN#
1	ORN/WHT	1
2	ORN	2
3		
4	BLU	4
5	BLU/WHT	5
6	GRN/WHT	3
7	GRN	6
8		
9	BRN/WHT	7
10	BRN	8
SHIELD	SHELL	SHELL

REVISION				
ZONE	REV	DESCRIPTION	DATE	CHANGED BY
	B	ECO-15276	02/05/2026	TDUFRENE
				DGUST

MODEL #	LENGTH		
	CM	M	FT
TRGIX605EC-BLK-20CM	20	.2	.66
TRGIX605EC-BLK-1M	100	1	3.28
TRGIX605EC-BLK-3M	300	3	9.84

IX INDUSTRIAL
TYPE A PLUG

CAT6a, 4 TWISTED PR, 26AWG STRANDED TINNED COPPER
WITH ALUM/POLY SHIELD (100%) WITH
TINNED COPPER DRAIN WIRE,
JACKET: POLYVINYLCHLORIDE, BLACK
CABLE O.D.: 0.233 NOM

RJ45 CAT6a
SHIELDED KEYSTONE
JACK/TEL POE+

NOTES:

CABLE CHARACTERISTICS:

TEMPERATURE RATING: -20°C TO +75°C

VOLTAGE RATING: 300 V

SHIELDED FLEXIBLE PATCH/JUMPER CABLE SUPPORTS SCREENED

568-C.2 CAT 6A APPLICATIONS

RECOMMENDATIONS IN TIA-568-C.2

RATING: NEC(UL)CMR/CMG

1. NOMINAL VOLTAGE: 50 V AC/ 60 V DC
2. IX CONNECTORS CONFORM TO IEC STANDARD 61076-3-124
3. THIS PRODUCT (TYPE A) IS DEFINED FOR 10/100 MBIT/S AND 1/10 GBIT/S ETHERNET COMMUNICATION.
4. RJ45 CONTACTS: 50um GOLD PLATED
5. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
6. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

6

5

4

3

2

1

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5] FRACTIONS
.XX = ±.02 [0.5] ± 1/32
.XXX = ±.005 [0.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = +1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINIT® brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE NONE SHEET 1 OF 1

DESCRIPTION

IXA-RJ45J, CAT6a F/UTP CMR/CMG PVC BLK

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	BPUCHASKI	TRGIX605EC-BLK	B