



IX PIN #	COLOR	RJ45 PIN#
1	ORN/WHT	1
2	ORN	2
3		
4	BLU	4
5	BLU/WHT	5
6	GRN/WHT	3
7	GRN	6
8		
9	BRN/WHT	7
10	BRN	8
SHIELD	SHELL	SHELL

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	12/15/2023	DZINN	GUTTADAURO

CAT6a, 4 TWISTED PR, 26AWG STRANDED TINNED COPPER WITH ALUM/POLY SHIELD (100%) OVER TINNED COPPER BRAID SHIELD (80%), JACKET: HIGH FLEX THERMOPLASTIC ELASTOMER, TEAL CABLE OD: .275 NOM.



C NOTES:

CABLE CHARACTERISTICS:

FLEX LIFE: 1 MILLION CYCLE TEST (10X CABLE O.D. MIN. RAD.)
10 MILLION CYCLE TEST (20X CABLE O.D. MIN. RAD.)

TEMPERATURE RATING: -40°C TO +75°C

VOLTAGE RATING: 300 V

POE COMPLIANT TO 70 METERS WHEN INSTALLED PER RECOMMENDATIONS IN TIA TSB-184.

FLAME RATING: CMX/CM OUTDOOR CABLE JACKET IS WELD SPATTER, SUNLIGHT (UV) AND CUTTING/MACHINING OIL RESISTANT.

1. NOMINAL VOLTAGE: 50 V AC/ 60 V DC
2. IX CONNECTORS CONFORM TO IEC STANDARD 61076-3-124
3. THIS PRODUCT (TYPE A) IS DEFINED FOR 10/100 MBIT/S AND 1/10 GBIT/S ETHERNET COMMUNICATION. PLEASE USE TYPE B FOR ALL OTHER NON ETHERNET APPLICATIONS LIKE SIGNALING, SERIAL OR OTHER INDUSTRIAL BUS COMMUNICATION SYSTEMS.
4. RJ45 CONTRACTS: 50µm GOLD PLATED.
5. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
6. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IAW L-COM PACKAGING SPECIFICATION PS-0031.
7. RJ45 ORIENTATION SHOWN FOR REF ONLY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5] FRACTIONS
XX = ±.02 [0.5] ± 1/32
XXX = ±.005 [0.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = +1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINITE brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5
SCALE SHEET
NONE 1 OF 1

RAUIXA-RJ45P CAT6A SF/UTP HI-FLEX CMX TPE TEAL

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DZINN	TRGIX609IN-TEL	A