




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION				
ZONE	REV	DESCRIPTION	DATE	CHANGED BY
	A	INITIAL RELEASE	09/02/2023	VTHANGARAJ
				GUTTADAURO




WIRING MAP	
C1	C2 WIRE COLOR
5	5 GRAY
4	4 BLACK
3	3 BLUE
2	2 WHITE
1	1 BROWN



- NOTES:**
1. IP: IP68 MATED 1M/24h
 2. CONNECTOR: THERMOPLASTIC, BLACK
 3. PIN: COPPER ALLOY, GOLD PLATED
 4. NUT: THERMOPLASTIC, BLACK
 5. OUTER MOLD: THERMOPLASTIC, BLACK
 6. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
 7. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

TABULATION BLOCK		
ITEM NUMBER	LENGTH METERS [FEET]	TOLERANCE INCH [mm]
TRGPB508-C2B-1M	1.0 [3.28]	+4.72 [+120]
TRGPB508-C2B-5M	5.0 [16.4]	±3.94 [±100]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		L-com™ an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936			
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [.13]		DRAWN BY VTHANGARAJ		09/02/2023					
		CHECKED BY DGUST		09/02/2023					
		APPROVED BY GUTTADAURO		09/02/2023					
THIRD-ANGLE PROJECTION 		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION IP69K WATERPROOF M12 5 POSITION B-CODE SENSOR SIGNAL CABLE, LIGHT WEIGHT PLASTIC NUT, 22 AWG, PVC, MALE TO RIGHT ANGLE FEMALE, BLACK					
				SIZE A		CAGE CODE 43321		ITEM NO. TRGPB508-C2B	
				SCALE: NONE		CAD FILE: TRGPB508-C2B.SLDDRW		SHEET 1 OF 1	