


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/18/2023	DFRISIELLO	GUTTADAURO



C14
IEC60320
BLACK

C13
IEC60320
BLACK

HygePlus
ANTI-MICROBIAL SJTOW3X18AWG
105°C, BLACK



ITEM NUMBER	LENGTH, FT [mm]	TOLERANCE
AMC14C13-10-3F	3.0 [915.0]	± .79 [20.0]
AMC14C13-10-6F	6.0 [1830.0]	± .79 [20.0]
AMC14C13-10-10F	10.0 [3050.0]	± .79 [20.0]

NOTES:

UL FILE: E234956
RATING: 10A/250V

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY: DFRISIELLO CHECKED BY: ELAMOTT APPROVED BY: GUTTADAURO	DATE 04/18/2023 04/18/2023 04/18/2023	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	CATEGORY POWER CORD			PRODUCT DESCRIPTION C14 to C13, Antimicrobe Jkt, 10 A	
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	SIZE: A CAGE CODE: 43321 SCALE: NONE		ITEM NO.: AMC14C13-10 CAD FILE: AMC14C13-10.SLDDRW