


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	ECO-13107	9/22/2023	DMAY	PHOSPODAR



ITEM NUMBER	LENGTH	
	METERS	FEET
AOC-4KHDMI-OM3PF-060	60	196.85

**NOTES:**

- CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:  
EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE:            ≤12 [305] = +1 [25] / -0            &gt;12 [305] ≤60 [1524] = +2 [51] / -0            &gt;60 [1524] ≤120 [3048] = +4 [102] / -0            &gt;120 [3048] ≤300 [7620] = +6 [152] / -0            &gt;300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES:            .X = ± .2 [5]   FRACTIONS ± 1/32            .XX = ± .02 [5]   ANGLES ± 1°            .XXX = ± .005 [1.3]</p> <p>THIRD-ANGLE PROJECTION</p>	<p>APPROVALS</p> <p>DRAWN BY DMAY</p> <p>CHECKED BY HBAKKE</p> <p>APPROVED BY PHOSPODAR</p>	<p>DATE</p> <p>06/12/2023</p> <p>06/15/2023</p> <p>06/15/2023</p>	<p><b>L-com</b> an INFINITI® brand</p> <p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p>
	<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p>		<p>CATEGORY</p> <p><b>FIBER OPTICS</b></p>
	<p>COLOR VARIATIONS MAY OCCUR</p>		<p>PRODUCT DESCRIPTION</p> <p><b>4K HDMI AOC OVER OM3 PURE FIBER, 60 METERS</b></p>
	<p>SIZE <b>A</b></p> <p>SCALE: NONE</p>	<p>CAGE CODE <b>43321</b></p> <p>CAD FILE: AOC-4KHDMI-OM3PF-060.SLDDRW</p>	<p>ITEM NO. <b>AOC-4KHDMI-OM3PF-060</b></p> <p>REV. <b>B</b></p>