



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	06/22/2023	BPUCHASKI	PHOSPODAR



HYBRID CABLE 4X FIBER AND COPPER WIRE
JACKET: PVC, BLACK: NOM. DIA. .19[4.8]

- NOTES:**
1. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY
 2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 an INFINITI® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	OVERALL CABLE LENGTH TOLERANCES: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY BPUCHASKI		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [1.3]	CHECKED BY JJOHNSTON	06/22/2023	CATEGORY FIBER OPTICS	
THIRD-ANGLE PROJECTION 	APPROVED BY PHOSPODAR	06/22/2023	PRODUCT DESCRIPTION DisplayPort 1.4 to Mini DisplayPort Active Optical Cable, 8K	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	CAGE CODE 43321
	COLOR VARIATIONS MAY OCCUR		ITEM NO. AOC-DPMDP8K	REV. A
			SCALE: NONE	CAD FILE: AOC-DPMDP8K.SLDDRW
			SHEET 1 OF 1	