


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	INITIAL RELEASE	04/24/2019	PHOSPODAR



Units in mm

10Gb/s SFP+ Active Optical Cable	LENGTH	
	METERS	FEET
AOCSP10-001	1.0	3.28
AOCSP10-002	2.0	6.56
AOCSP10-003	3.0	9.84
AOCSP10-005	5.0	16.40
AOCSP10-007	7.0	22.97
AOCSP10-010	10.0	32.81
AOCSP10-020	20.0	65.62
AOCSP10-050	50.0	164.04
AOCSP10-100	100.0	328.08

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  
 OVERALL CABLE LENGTH TOLERANCE:  
 ≤12 [305] = +1 [25] / -0  
 >12 [305] ≤60 [1524] = +2[51] / -0  
 >60 [1524] ≤120 [3048] = +4 [102] / -0  
 >120 [3048] ≤300 [7620] = +6 [152] / -0  
 >300 [7620] = +5% / -0%  
 ALL OTHER DIMENSIONAL TOLERANCES:  
 .X = ±.2 [5.08]  
 .XX = ±.02 [5.1]  
 .XXX = ±.005 [1.3]



APPROVALS	DATE
DRAWN BY DZINN	04/22/2019
CHECKED BY DFRISIELLO	04/22/2019
APPROVED BY PHOSPODAR	04/22/2019

**L-com** Global Connectivity  
 50 HIGH STREET  
 NORTH ANDOVER, MA  
 01845

CATEGORY FIBER OPTICS			
PRODUCT DESCRIPTION Active Optical Cable SFP+ 10Gb/s			
SIZE <b>B</b>	FSCM NO. <b>43321</b>	DWG. NO. AOCSP10	REV. A
SCALE: 1:4	CAD FILE AOCSP10.SLDDRW	SHEET 1 OF 1	